

16 Port High Resolution VGA Video Splitter - 400 MHz

Product ID: ST1216PRO



This high resolution VGA splitter offers a practical solution for high-res multi-screen presentations, allowing a VGA video signal to be broadcast from a computer to up to 16 VGA monitors simultaneously.

The VGA splitter is ideal for classrooms, tradeshow, in-store displays or any application where high quality video on multiple monitors is required, supporting displays with up to 400 MHz of video bandwidth and high resolution applications up to 2048 x 1536.

To help ensure high quality VGA video even at longer distances, the high resolution VGA splitter features a built-in booster circuit that allows monitors to be located up to 210ft away from the host system.

Designed for simplicity and convenience, the VGA splitter offers easy plug and play installation; a completely hardware-based solution, the VGA splitter requires no software operation, saving both time and hassle.

Backed by our 2-year warranty and free lifetime technical support, this high-resolution VGA splitter lets you get the most out of your video content with quality construction you can depend on.

Certifications, Reports and Compatibility

Applications

- In-store product merchandising
- Information booths/kiosks
- Trade-shows
- Lecture halls and classrooms

- Airports, bus terminals and train stations

Features

- Compatible with VGA, SVGA and Multisync monitors
- 400 MHz bandwidth provides brilliant 2048 x 1536 resolution
- DDC,DDC2 & DDC2B compatible (on Video Out port 1)
- Includes DC 7.5V power adapter and rack mounting brackets
- Daisy chainable for almost unlimited expansion
- Uses standard monitor extension cables (StarTech.com coaxial VGA cables recommended for best picture quality)

Hardware

Warranty	2 Years
Ports	16
Daisy-Chain	Yes

Performance

Maximum Cable Length	213.2 ft [65 m]
Maximum Analog Resolutions	2048x1536 @ 60Hz
Bandwidth	400MHz

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Special Notes / Requirements

Note	Units made before August 2008 shipped with a DC 7.5V 1500mA (max) power adapter
------	---

Power

Power Source	AC Adapter Included
Output Voltage	12V DC
Output Current	1.2A



Power Consumption (In Watts)	14.4
------------------------------	------

Physical Characteristics

Color	Silver
Product Length	14.7 in [37.3 cm]
Product Width	3.0 in [75.0 mm]
Product Height	1.7 in [42.0 mm]
Weight of Product	5.2 oz [148.0 g]

Packaging Information

Package Length	17.6 in [44.8 cm]
Package Width	3.6 in [92.0 mm]
Package Height	6.0 in [15.2 cm]
Shipping (Package) Weight	15.4 oz [435.0 g]

What's in the Box

Included in Package	16 Port Rack Mount VGA Splitter
	Mounting Brackets
	Mounting Screws
	Universal Power Adapter (NA/UK/EU)
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

