

## Multi-Input HDBaseT Extender Kit with Built-In Switch and Video Scaler - TAA

**Product ID:** ST121HDBTSC



This multi-input HDBaseT extender kit extends your A/V signals to a remote location up to 230 ft. (70 m) away. It features a built-in switch and scaler, so you can choose which video source is output from four independent video sources (2 x HDMI, 1 x VGA and 1 x DisplayPort).

The HDBaseT extender's built-in converter switch lets you connect two HDMI sources, a VGA source, and a DP source to the same remote and local HDMI display. You don't need adapters or scalers, or a video switch.


Along with manually switching your video source with easy-to-use buttons, the video extender ensures hassle-free operation with two auto-switching modes: auto-detect switching, which detects and selects a newly connected device, and priority selection, which lets you choose which port is activated by default, for automatic switching.

This HDBaseT extender features a built-in scaler that scales the image to 1080p, so you can rest assured your HDMI display will intuitively work with any source that's connected through it. Scaling is easy to do, with an intuitive OSD that's accessible using buttons on the remote receiver. Newer HDMI displays no longer support legacy resolution video signals. Without support for these common VGA resolutions, your source may not work with your new HDMI display.

The extender kit maintains your HD picture quality, even at 230 ft. (70 m) away from your video source, ensuring you can provide the best possible viewing experience.

The ST121HDBTSC is backed by a 2-year StarTech.com warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



## Applications

- Create brilliant digital signage displays in large public settings such as hospitals, shopping centers or stadiums
- Automatically switch between your set-top box or computer, for remote entertainment displays, in hospitality settings such as restaurants, bars or hotels

## Features

- Save hassle and expense with a switch and extender in one device, that accommodates VGA, DP and HDMI inputs
- Ensure perfect video connectivity, every time, with a built-in video scaler
- Get crystal-clear picture quality at impressive distances with 1080 resolution at up to 230 ft.

---

### Hardware

Warranty	2 Years
Cabling	Cat 5e UTP or better
Audio	Yes
Rack-Mountable	Yes
Daisy-Chain	No

---

### Performance

Maximum Cable Length	229.6 ft [70 m]
Max Distance	70m [230ft]
Maximum Digital Resolutions	1920x1200 @ 60 Hz
Supported Resolutions	1920x1200 @ 60 Hz, 1920x1080 (1080p), 1680x1050, 1600x1200, 1440x900, 1400x1050, 1366x768, 1280x800, 1360x768, 1280x1024, 1280x720 (720p), 1024x768, 800x600, 640x480
	Lower resolutions and refresh rates are also supported.
Wide Screen Supported	Yes
Audio Specifications	2-channel

---

### Connector(s)

Local Unit Connectors	2 - HDMI (19 pin)
-----------------------	-------------------

- 1 - DisplayPort (20 pin)
- 1 - VGA (15 pin, High Density D-Sub)
- 1 - 3.5 mm Mini-Jack (3 Position)
- 1 - HDMI (19 pin)
- 2 - IrDA (Infrared, SIR/FIR)
- 1 - RJ-45
- 1 - RJ-11
- Remote Unit Connectors
- 1 - RJ-45
- 1 - HDMI (19 pin)
- 1 - RJ-11

---

## Indicators

- |                |                                      |
|----------------|--------------------------------------|
| LED Indicators | 4 - selected port LEDs (transmitter) |
|                | 2 - status LEDs (transmitter)        |
|                | 4 - input LEDs (receiver)            |
|                | 1 - status LED (receiver)            |
|                | 4 - selected port LEDs (receiver)    |

---

## Power

- |                              |                     |
|------------------------------|---------------------|
| Power Source                 | AC Adapter Included |
| Input Voltage                | 100 - 240 AC        |
| Input Current                | 0.6 A               |
| Output Voltage               | 12V DC              |
| Output Current               | 1.5 A               |
| Center Tip Polarity          | Positive            |
| Plug Type                    | M                   |
| Power Consumption (In Watts) | 18                  |

---

## Environmental

Operating Temperature	0 to 40C (32F to 104F)
Storage Temperature	-10 to 60C (14F to 140F)
Humidity	0% - 80 % RH (non-condensing)

---

## Physical Characteristics

Color	Black
Material	Aluminum
Product Length	4.2 in [10.6 cm]
Product Width	2.4 in [6.1 cm]
Product Height	2.6 in [6.7 cm]
Weight of Product	4.5 lb [2.0 kg]

---

## Packaging Information

Package Quantity	1
Package Length	6.3 in [16.0 cm]
Package Width	3.9 in [9.8 cm]
Package Height	1.6 in [4.0 cm]
Shipping (Package) Weight	2.4 lb [1.1 kg]

---

## What's in the Box

Included in Package	1 - HDBaseT transmitter
	1 - HDBaseT scaler receiver
	1 - remote control
	1 - RJ-11 to RS-232 adapter
	1 - RJ-11 cable
	2 - sets of mounting brackets
	1 - universal power adapter (NA/JP, EU, UK, ANZ)

1 - IR blaster

1 - IR receiver

2 - sets of rubber feet

1 - quick-start guide

---

***\*Product appearance and specifications are subject to change without notice.***