

Multi-Input HDBaseT Extender Kit with Built-In Switch and Video Scaler

Product ID: ST121HDBTSC



This multi-input HDBaseT extender kit extends your A/V signals to a remote location up to 230 ft. (70 m) away. It features a built-in switch and scaler, so you can choose which video source is output from four independent video sources (2 x HDMI, 1 x VGA and 1 x DisplayPort).

The HDBaseT extender's built-in converter switch lets you connect two HDMI sources, a VGA source, and a DP source to the same remote and local HDMI display. You don't need adapters or scalers, or a video switch.

Along with manually switching your video source with easy-to-use buttons, the video extender ensures hassle-free operation with two auto-switching modes: auto-detect switching, which detects and selects a newly connected device, and priority selection, which lets you choose which port is activated by default, for automatic switching.

This HDBaseT extender features a built-in scaler that scales the image to 1080p, so you can rest assured your HDMI display will intuitively work with any source that's connected through it. Scaling is easy to do, with an intuitive OSD that's accessible using buttons on the remote receiver. Newer HDMI displays no longer support legacy resolution video signals. Without support for these common VGA resolutions, your source may not work with your new HDMI display.

The extender kit maintains your HD picture quality, even at 230ft. (70 m) away from your video source, ensuring you can provide the best possible viewing experience.

The ST121HDBTSC is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Automatically switch between your set-top box or computer, for remote entertainment displays, in hospitality settings such as restaurants, bars or hotels
- Create brilliant digital signage displays in large public settings such as hospitals, shopping centers or stadiums

Features

- Save hassle and expense with a switch and extender in one device, that accommodates VGA, DP and HDMI inputs
- Ensure perfect video connectivity, every time, with a built-in video scaler
- Get crystal-clear picture quality at impressive distances with 1080 resolution at up to 230 ft.

Hardware	Warranty	2 Years
	Cabling	Cat 5e UTP or better
	Audio	Yes
	Rack-Mountable	Yes
	Daisy-Chain	No
Performance	Maximum Cable Length	229.6 ft [70 m]
	Max Distance	70 m / 230 ft
	Maximum Digital Resolutions	1920x1200 @ 60 Hz
	Supported Resolutions	1920x1200 @ 60 Hz, 1920x1080 (1080p), 1680x1050, 1600x1200, 1440x900, 1400x1050, 1366x768, 1280x800, 1360x768, 1280x1024, 1280x720 (720p), 1024x768, 800x600, 640x480
	Wide Screen Supported	
	Audio Specifications	<i>Lower resolutions and refresh rates are also supported.
		Yes 2-channel
Connector(s)	Local Unit Connectors	HDMI (19 pin)
	Local Unit Connectors	DisplayPort (20 pin)
	Local Unit Connectors	VGA (15 pin, High Density D-Sub)
	Local Unit Connectors	3.5 mm Mini-Jack (3 Position)
	Local Unit Connectors	HDMI (19 pin)
	Local Unit Connectors	IrDA (Infrared, SIR/FIR)
	Local Unit Connectors	RJ-45
	Local Unit Connectors	RJ-11
	Remote Unit Connectors	RJ-45

Remote Unit Connectors HDMI (19 pin)

Remote Unit Connectors RJ-11

Indicators	LED Indicators	selected port LEDs (transmitter)
	LED Indicators	status LEDs (transmitter)
	LED Indicators	input LEDs (receiver)
	LED Indicators	status LED (receiver)
	LED Indicators	selected port LEDs (receiver)

Power	Power Source	AC Adapter Included
	Input Voltage	100 - 240 AC
	Input Current	0.6 A
	Output Voltage	12V DC
	Output Current	1.5 A
	Center Tip Polarity	Positive
	Plug Type	M
	Power Consumption (In Watts)	18

Environmental	Operating Temperature	0 to 40C (32F to 104F)
	Storage Temperature	-10 to 60C (14F to 140F)
	Humidity	0% - 80 % RH (non-condensing)

Physical Characteristics	Color	Black
	Material	Aluminum
	Product Length	4.2 in [1.1 cm]
	Product Width	2.4 in [61 mm]
	Product Height	2.6 in [67 mm]
	Weight of Product	4.5 lb [2.0 kg]

Packaging Information	Package Quantity	1
	Package Length	6.3 in [1.6 cm]
	Package Width	3.9 in [98 mm]
	Package Height	1.6 in [40 mm]



Shipping (Package)
Weight 2.4 lb [1.1 kg]

What's in the Box	Included in Package	HDBaseT transmitter
	Included in Package	HDBaseT scaler receiver
	Included in Package	RJ-11 to RS-232 adapter
	Included in Package	remote control
	Included in Package	RJ-11 cable
	Included in Package	sets of mounting brackets
	Included in Package	universal power adapter (NA/JP, EU, UK, ANZ)
	Included in Package	sets of rubber feet
	Included in Package	quick-start guide
	Included in Package	IR blaster
	Included in Package	IR receiver

****Product appearance and specifications are subject to change without notice.***

