

VGA Video extender / Transmitter Receiver über Cat5 und bis max. 150m

Produkt-ID: ST121R



The ST121R VGA over Cat5 Video Extender Receiver is specifically designed for use as the receiver unit to the StarTech.com ST1214T 4 Port, and ST1218T 8 Port VGA over Cat5 UTP Extender transmitter units, allowing you to split and extend a single VGA source to up to four remote displays.

From the transmitter device, the VGA video signal is sent over standard 4 pair Category 5 or better UTP cable to remote monitors, each connected to an ST121R Cat 5 VGA receiver - supporting distances of up to 150 meters (500 feet).

A cost-effective video extension solution, this receiver is ideal for a wide range of environments including airports, bus depots, retail, or any large buildings where VGA video needs to be extended to long connection distances.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment

- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at tradeshow and in auditoriums

Merkmale

- Extends video cables by up to 500 ft. (150m)
- Pure hardware design, no software or drivers required
- Included mounting brackets
- Uses standard Category 5 straight-wired, twisted-pair, network patch cable for economical and reliable data transmission

Hardware

Garantiebestimmungen	2 Years
Ports	1
Kabel	Cat5 UTP oder höher
Audio	Nein
Reihenschaltung	Nein

Leistung

Max. Kabellänge	500.0 ft [152.4 m]
Max. Entfernung	150m [492ft]
Max. Analogauflösungen	1024x768
Unterstützte Auflösungen	1600x1200 @ 150ft(50m) 1280x1024 @ 300ft(100m) 1024x768 @ 500ft(150m)

Steckverbinder

Remote-Gerät-Anschlü	1 - RJ-45
----------------------	-----------

sse

2 - VGA (15-polig, High Density D-Sub)

Strom

Stromversorgung	Mit Netzadapter
Eingangsspannung	100 - 240 AC
Eingangsstrom	0.2A
Ausgangsspannung	12V DC
Ausgangsstrom	0.5A
Polarität der Mittelspitze	Positiv
Steckertyp	M
Stromverbrauch	6

Physische Eigenschaften

Farbe	Schwarz
Gehäusety	Aluminium
Produktlänge	3.3 in [8.4 cm]
Produktbreite	2.6 in [6.5 cm]
Produkthöhe	0.8 in [2.1 cm]
Produktgewicht	5.9 oz [168.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	8.7 in [22.0 cm]
Paketbreite	4.1 in [10.4 cm]
Pakethöhe	3.9 in [9.8 cm]
Versandgewicht	1.2 lb [0.5 kg]

(Verpackung)

Verpackungsinhalt

Im Paket enthalten	1 - REMOTE UNIT VGA EXTENDER
	1 - 9V AC 500ma ADAPTORS
	1 - INSTRUCTION MANUAL

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.