

VGA Video extender über Cat5 bis zu 130m und mit einer Auflösung von 1600x1200@80m

Produkt-ID: ST121UTP



The ST121UTP VGA Video Extender over Cat5 allows you to extend your VGA video signal by up to 150 meters (500 feet) and connect up to 4 displays (2 local and 2 remote) from that single source. The ST121UTP is a bundled kit including both a local transmitter and a remote receiver unit, offering a complete solution for scenarios in which remote monitor displays are required.

The local unit features a single VGA input as well as two VGA outputs giving you the ability to view and split your source VGA signal to two independent displays locally. The VGA video signal is then sent over standard 4 pair Category 5 or better UTP cable to the remote unit which also features two additional VGA outputs giving you the freedom to display your VGA source on up to four monitors in total.

The included a mounting bracket for the ST121UTP receiver provides versatile mounting options such as a wall, desk or cabinet.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at tradeshow and in auditoriums

Merkmale

- Consists of 1 Base unit for the local display, and 1 Remote unit for the remote display (up to 2 monitors can be connected at each location)
- Extends video cables by up to 500 ft. (150m)
- Uses standard Category 5 straight-wired, twisted-pair, network patch cable for economical and reliable data transmission
- Included mounting brackets

Hardware

Garantiebestimmungen	2 Years
Ports	1
Kabel	Cat5e UTP oder höher
Audio	Nein
Reihenschaltung	Nein

Leistung

Max. Entfernung	150m [492ft]
Unterstützte Auflösungen	1440x900 @ 150ft / 50m 1280x1024 @ 300ft / 100m 1024x768 @ 500ft / 150m

Steckverbinder

Anschlüsse lokales Gerät	1 - RJ-45
--------------------------	-----------

1 - VGA (15-polig, High Density D-Sub)

2 - VGA (15-polig, High Density D-Sub)

Remote-Gerät-Anschlüsse 1 - RJ-45

2 - VGA (15-polig, High Density D-Sub)

Strom

Stromversorgung	Mit Netzadapter
Ausgangsspannung	9V DC
Ausgangsstrom	0.6A
Polarität der Mittelspitze	Positiv
Steckertyp	M
Stromverbrauch	5.4

Umgebungsbedingungen

Betriebstemperatur	0°C to 50°C (32°F to 122°F)
Lagertemperatur	-20°C to 60°C (-4°F to 140°F)
Feuchtigkeit	0 bis 80% relative Luftfeuchtigkeit, nicht kondensierend

Physische Eigenschaften

Farbe	Schwarz
Gehäusotyp	Aluminium
Produktlänge	2.4 in [6.0 cm]
Produktbreite	3.3 in [8.3 cm]
Produkthöhe	0.8 in [2.0 cm]
Produktgewicht	11.8 oz [335.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.4 in [18.8 cm]
Paketbreite	9.5 in [24.2 cm]
Pakethöhe	3.7 in [9.3 cm]
Versandgewicht (Verpackung)	2.1 lb [0.9 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Local VGA Extender Unit
	1 - Remote VGA Extender Unit
	1 - Mounting Bracket for Receiver (w/ screws)
	2 - Sets Rubber Feet
	2 - Power Adapter
	1 - Instruction Manual

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.