

DVI Video Extender over Cat 5 UTP

Produkt ID: ST121UTPDVI



The ST121UTPDVI DVI Video Extender over Cat 5 UTP lets you extend a DVI Digital (DVI-D) video signal over Category 5 (or better) cable at distances of up to 150-feet (45-meters) from the video source to the intended display, without sacrificing video quality.

This cost-effective video extender is simple to use and offers a compact form factor, helping to save valuable work space.

With support for resolutions up to 1600x1200, this DVI extender can be easily integrated using existing Ethernet infrastructure wiring, and offers a completely hardware-based solution with no software or drivers required - perfect for any small scale point-to-point digital signage application that requires high quality DVI video.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, business and retail/POS sectors

Funktioner

- Consists of 1 local unit, and 1 remote unit for an all-in-one solution
- Extends video signal over standard Category 5 UTP cable
- Supports resolutions up to 1600x1200 @ 60Hz
- Supports DVI-D interface

Hårdvara

Garantipolicy	2 Years
Portar	1
Kablage	Cat 5 UTP eller bättre
Audio	Nej
Kedjekoppling	Nej

Prestanda

Maximalt avstånd	45m [148ft]
Maximal digital upplösning	1600x1200 @ 60Hz
Medeltid mellan fel (MTBF)	180.102 timmar

Kontakt(er)

Lokala enhetskontakter	1 - DVI-I (29-stifts)
	1 - RJ-45
Fjärrenhetskontakter	1 - DVI-I (29-stifts)
	1 - RJ-45

Särskilda anmärkningar/krav

Obs.	DVI-A (Analog) signal not supported
------	-------------------------------------

Ström

Strömkälla	2 AC-adaptrar medföljer
Inspänning	100 - 240 AC
Inström	0.2A
Utspanning	5 DC
Utström	1A
Polaritet på mittpol	Positiv
Kontakttyp	H
Strömförbrukning	5

Miljö

Drifttemperatur	32° to 122° F (0° to 50° C)
Förvaringstemperatur	-4° to 158° F (-20 to 70° C)
Luftfuktighet	15 to 90% relative humidity, non-condensing

Utseende

Färg	Svart
Kabinettyp	Stål
Produktlängd	2.6 in [6.7 cm]
Produktbredd	2.0 in [5.2 cm]
Produkthöjd	1.5 in [3.8 cm]
Produktvikt	10.1 oz [285.5 g]

Förpackning

Förpackningsantal	1
Paketets längd	9.6 in [24.4 cm]
Paketets bredd	2.6 in [6.7 cm]
Paketets höjd	6.1 in [15.5 cm]
Fraktvikt (förpackning)	1.4 lb [0.6 kg]

Vad det är i lådan

Ingår i paketet

1 - DVI Local Unit Extender

1 - DVI Remote Unit Extender

2 - Power Adapters

1 - Instruction Manual

Warranty
Information

Warranty

2 År

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.