

Wireless HD Extender WHDI - 1080p Wireless High Definition 100 ft / 30m

Product ID: ST121WHD



The ST121WHD Wireless HD Video Extender Kit includes both a WHDI transmitter and WHDI receiver, enabling you to wirelessly send a full HD (1080p) video signal, as well as audio and IR, from a high-definition signal source to a remote HD display or projector located up to 30m (100ft) away.

The ST121WHD is a bundled kit, which provides both local and remote units, and an IR remote control, delivering a complete, end-to-end alternative for a single source-to-display digital signage connection.

A cost-effective solution, the wireless HD extender delivers full High-Definition video, as well as audio and Infrared (IR), eliminating the need for an expensive cable infrastructure to provide a wireless solution for settings where cabling may be undesirable, (e.g. in the middle of a room, boardroom, etc.) or difficult to install.

Compliant with both HDCP, and WHDI standards, this versatile WHDI transmitter/receiver kit ensures that even the latest devices will be able to pass a signal, with support for full 1080p resolutions and the accompanying digital audio. Plus, the kit enables you to control your source device remotely, using the IR extender for a complete HD extension solution.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environments (e.g. industrial sites)

- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at tradeshow and in auditoriums

Features

- Extend HD video up to 100ft (30m)
- Includes WHDI transmitter (local) and WHDI receiver (remote) units
- Supports resolutions up to 1080p (1920x1080)
- Pure hardware design - no software or drivers required
- IR remote control enables you to control your source device remotely through the wireless connection back to the transmitter

Hardware

Warranty	2 Years
Ports	1
Cabling	Wireless Ethernet
Audio	Yes
Daisy-Chain	No

Performance

Max Distance	30 m / 100 ft
Maximum Digital Resolutions	1920x1080
Supported Resolutions	Widescreen: 1080p, 1080i, 720p, 480p , Standard: VGA(640X480), SVGA(800X600), XGA(1024X768), SXGA(1280X1024)

Connector(s)

Local Unit Connectors	HDMI (19 pin)
Remote Unit Connectors	HDMI (19 pin)

Special Notes / Requirements

Note	The maximum distance between the transmitter and the receiver
------	---

is 30 meters. If the wireless signal is obstructed by walls, or other interference the signal quality and maximum distance will likely be reduced. The working Frequency band may vary with the relevant laws in different regions.

Indicators

LED Indicators	Wireless Network Status Indicator
	Video Status Indicator

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	M

Environmental

Operating Temperature	0~40C
Storage Temperature	-20~60C
Humidity	5% ~ 90% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Length	5.8 in [14.8 cm]
Product Width	3.8 in [97 mm]
Product Height	0.7 in [18 mm]
Weight of Product	15.5 oz [440 g]

Packaging Information

Package Length	10.6 in [27 cm]
----------------	-----------------



Package Width	7.9 in [20 cm]
Package Height	3.5 in [90 mm]
Shipping (Package) Weight	3.2 lb [1.4 kg]

What's in the Box

Included in Package	Wireless HD Transmitter
	Wireless HD Receiver
	IR Remote Control
	Positioning Stand
	HD Cable
	IR Remote Extension Connector
	Universal Power Adapter (NA/UK/EU/AUS)
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

