

2 Port DVI Video Splitter with Audio - TAA

Produkt ID: ST122DVIA



The ST122DVIA DVI splitter lets you share one DVI video and audio source on two displays and acts as a signal amplifier that allows you to locate your DVI monitors up to 33ft (10 m) away from your computer or DVI signal source.

With support for high definition resolutions up to 1080p (HDTV)/1920x1200 (PC), the DVI splitter delivers a simple and convenient DVI video solution that suits virtually any application or operating environment (classroom, healthcare, professional A/V, control centres, retail POS environments).

The DVI video splitter/distribution amplifier is easy to install, providing you with flawless digital video that will help you get the most from your DVI-enabled monitors, projectors, or plasma screens.

This product is TAA compliant and backed by StarTech.com's 2-year warranty with FREE lifetime tech support.

Certifikat, rapporter och kompatibilitet



Användning

- Connect DVI projectors, monitors, large displays, and wall display systems for digital signage applications and ensuring content is delivered to target audience.
- Great for use in tradeshow, POS retail, healthcare, transportation terminals, education, house of

worship.

Funktioner

- Supports resolutions of up to 1920 x 1200 pixels @ 60 Hz
- Split both video and 3.5mm analog stereo audio
- DVI, and HDCP compliant for easier HD video distribution
- Accurate and reliable reproduction of digital video signal, with no signal attenuation or distortion
- Easy setup for a quick connection in minutes

Hårdvara

Garantipolicy	2 Years
AV-ingång	DVI
Portar	2
AV-utgång	DVI
Kablage	DVI
Industristandarder	DVI 1.0, and HDCP 1.1

Prestanda

Maximalt avstånd	10m [33ft]
Maximal digital upplösning	1920x1200 @ 60Hz
Stöd för widescreen	Ja

Kontakt(er)

Connector A	1 - 3.5 mm minijack (3-polig)
	1 - DVI-I (29-stifts)
Connector B	2 - 3.5 mm minijack (3-polig)
	2 - DVI-I (29-stifts)

Indikatorer

LED-indikatorer	1 - Green - Power/Link
	2 - Green - Link

Ström

Strömkälla	AC-adapter medföljer
Inström	0.6A
Utspanning	12V DC
Utström	1.5A
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	18W

Miljö

Drifttemperatur	0°C to 40°C (32°F to 104°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
Luftfuktighet	0~80% RH

Utseende

Färg	Svart
Kabinetttyp	Aluminium
Produktlängd	7.1 in [18.1 cm]
Produktbredd	3.4 in [8.5 cm]
Produkthöjd	0.8 in [2.0 cm]
Produktvikt	14.2 oz [401.0 g]

Förpackning

Förpackningsantal	1
Paketets längd	8.7 in [22.1 cm]
Paketets bredd	3.9 in [10.0 cm]

Paketets höjd 3.9 in [10.0 cm]

Fraktvikt (förpackning) 1.6 lb [0.7 kg]

Vad det är i lådan

Ingår i paketet	1 - DVI splitter
	4 - rubber feet
	1 - universal power adapter (NA, EU, UK, ANZ)
	1 - instruction manual

Warranty
Information

Warranty	2 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.