

2 Port HDMI Video Splitter with Audio - USB Powered

Product ID: ST122HDMILE



The ST122HDMILE 2-Port HDMI Video Splitter with Audio lets you share a single high definition video and audio source between two HDMI or DVI (with HDMI to DVI cable) displays. The HDMI splitter is USB-powered, making it ideal for use with desktop and laptop computers that offer HDMI output.

The USB powered High Speed HDMI splitter is HDCP 1.1 compliant, delivering outstanding audio capability and flawless digital video at resolutions of up to 1080p.

To overcome connection distance limitations, the HDMI splitter also functions as an HDMI distribution amplifier allowing you to situate HDMI monitors up to 45ft (15m) away from the HDMI source - a perfect solution for connecting an HDMI-capable computer to monitors, projectors or plasma screens as needed.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connecting multiple HDMI enabled projectors, LCD Displays, and Plasma Displays from a single PC source
- Ideal for classroom settings, where educators can display their computer screen on multiple displays for better visibility
- Perfect for corporate boardrooms that employ multiple screens or projectors
- Set up your trade show display with multiple screens
- Use in retail environments for advertising or training

Features

- High Speed HDMI and HDCP 1.1 compliant
- Splits an HDMI source to 2 outputs, without signal loss
- Supports a wide range of HDTV resolutions, from 480p to 1080p
- Compact design
- USB-powered - no wall outlet or bulky power supply required
- Integrated signal amplifier - situate displays up to 45ft(15m) away

Hardware	Warranty	2 Years
	AV Input	HDMI
	Ports	2
	AV Output	HDMI
	Industry Standards	High Speed HDMI, HDCP
	Daisy-Chain	Yes
Performance	Maximum Cable Length	49.2 ft [15 m]
	Supported Resolutions	480p, 480i, 720p, 1080i, 1080p
	Wide Screen Supported	1600x1200(UXGA)
		Yes
Connector(s)	Connector A	HDMI (19 pin)
	Connector A	USB Type-A (4 pin) USB 2.0
	Connector B	HDMI (19 pin)
Special Notes / Requirements	System and Cable Requirements	An HDMI source (desktop / laptop) with a USB port for powering ST122LE.
Indicators	LED Indicators	Power
Power	Power Source	USB-Powered
	Input Voltage	5 DC
	Input Current	500mA
Environmental	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-20C to 85C (-4F to 185F)
	Humidity	0~95% RH
Physical Characteristics	Color	Black

Material	Plastic
Cable Length	11.0 in [2.8 cm]
Product Length	3.0 in [75 mm]
Product Width	2.0 in [50 mm]
Product Height	1.0 in [25 mm]
Weight of Product	2.7 oz [76 g]

Packaging Information	Package Length	8.3 in [2.1 cm]
	Package Width	5.7 in [1.4 cm]
	Package Height	1.6 in [40 mm]
	Shipping (Package) Weight	7.7 oz [219 g]

What's in the Box	Included in Package	HDMI Splitter
	Included in Package	Instruction Manual
	Included in Package	24" USB Power cable

****Product appearance and specifications are subject to change without notice.***

