

## 2 Port VGA Video Splitter - 250 MHz

**Product ID:** ST122L



The ST122L 2 Port VGA Video Splitter allows a single VGA source to display VGA video onto two monitors simultaneously. Perfect for classrooms, tradeshow, or in-store displays where high quality video on several monitors is needed. The simple plug and play operation makes setup quick and easy so you can be up and running in minutes.

The ST122L supports displays with up to 250 MHz of bandwidth, providing brilliant resolutions up to 1920x1440. A built-in booster circuit lets you situate your displays up to 210 ft away from your source.

Backed by a StarTech.com 2-year warranty and free lifetime technical support. Male to Female VGA extension cable required (MXT101HQ)

## Certifications, Reports and Compatibility

### Applications

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

### Features

- Supports resolutions up to 1920x1440

- Maximum cable distance 210 feet (65m)
- Supports Cascading up to 3 levels
- 250 MHz video bandwidth
- Compatible with VGA, SVGA and Multisync monitors

---

#### Hardware

Warranty	2 Years
Ports	2
AV Input	VGA
AV Output	VGA
Audio	No
Daisy-Chain	Yes

---

#### Performance

Maximum Cable Length	213.2 ft [65 m]
Maximum Analog Resolutions	1920x1440
Bandwidth	250 MHz
General Specifications	Male to Female VGA extension cable required (MXT101HQ)

---

#### Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

---

#### Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.3
Output Voltage	9V DC
Output Current	0.8



Center Tip Polarity Positive

Plug Type M

---

**Environmental**

Operating Temperature 0C to 40C (32F to 104F)

Storage Temperature -20C to 60C (-4F to 140F)

Humidity 0~90% RH, non-condensing

---

**Physical Characteristics**

Color Black

Material Steel

Product Length 2.6 in [65.0 mm]

Product Width 5.2 in [13.1 cm]

Product Height 1.0 in [25.9 mm]

Weight of Product 7.8 oz [221 g]

---

**Packaging Information**

Package Length 10.8 in [27.4 cm]

Package Width 3.2 in [81 mm]

Package Height 7.5 in [19 cm]

Shipping (Package) Weight 29.7 oz [840 g]

---

**What's in the Box**

Included in Package 2 Port VGA Splitter

Power Adapter

User Manual

---

*\*Product appearance and specifications are subject to change without notice.*

