

2 Port VGA Video Splitter - USB Powered

Product ID: ST122LE



This 2-Port VGA Video Splitter allows a computer to display VGA video on two monitors simultaneously.

Perfect for classrooms, tradeshows, or any environment requiring high quality video on several monitors, the ST122LE VGA splitter supports displays with up to 300 MHz of bandwidth and up to 2048x1536 resolution. Plus, to simplify placement of your VGA displays, the splitter features a built-in booster circuit that allows you to locate VGA monitors up to 200 ft away from your system, and can be powered through a USB connection to the host computer, eliminating the need to find an available power outlet.

The ST122LE VGA Splitter supports easy plug and play installation, and is backed by StarTech.com's 2-year warranty and FREE lifetime tech support.

Certifications, Reports and Compatibility



Applications

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility
- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

Features

- Integrated signal amplifier boosts your connection range to 200 feet (60 meters)
- 300 MHz video bandwidth

- Supports DDC, DDC2, DDC2B (For video out port 1)
- Our most compact VGA splitter
- USB-Powered
- Supports resolutions up to 2048 x 1536 @60Hz

Hardware	Warranty	2 Years
	Ports	2
	Industry Standards	DDC, DDC2, DDC2B, on Video Out Port 1

Performance	Maximum Cable Length	199.9 ft [61.0 m]
	Maximum Analog Resolutions	2048x1536
	Bandwidth	300MHz
	MTBF	40,000 Hours

Connector(s)	Connector A	VGA (15 pin, High Density D-Sub)
	Connector B	VGA (15 pin, High Density D-Sub)

Power	Power Source	USB-Powered
	Output Voltage	5 DC
	Output Current	0.5A
	Center Tip Polarity	Positive
	Plug Type	M

Environmental	Operating Temperature	0C to 70C (32F to 158F)
	Storage Temperature	-20C to 85C (-4F to 185F)
	Humidity	0% - 95%

Physical Characteristics	Color	Black
	Material	Plastic
	Weight of Product	3.5 oz [100 g]

Packaging Information	Package Length	8.3 in [2.1 cm]
	Package Width	5.7 in [1.4 cm]
	Package Height	1.6 in [40 mm]
	Shipping (Package) Weight	8.3 oz [235 g]



What's in the Box	Included in Package	Video Splitter
	Included in Package	USB to DC power adapter
	Included in Package	User Manual

****Product appearance and specifications are subject to change without notice.***

