

## 2 Port High Resolution VGA Video Splitter with Audio - 400 MHz

**Product ID:** ST122PROA



This high resolution VGA splitter offers a practical solution for high-res multi-screen presentations, allowing a VGA video signal as well as the corresponding audio to be broadcast from a computer to up to two sets of VGA monitors and speakers simultaneously.

The VGA splitter is ideal for classrooms, tradeshow, in-store displays or any application where high quality video and audio is required, supporting displays with up to 400 MHz of video bandwidth and high resolution applications up to 2048 x 1536.

To help ensure high quality VGA video even at longer distances, the high resolution VGA splitter features a built-in booster circuit that allows monitors to be located up to 210ft away from the host system.

Designed for simplicity and convenience, the VGA splitter offers easy plug and play installation; a completely hardware-based solution, the VGA splitter requires no software operation, saving both time and hassle.

Backed by our 2-year warranty and free lifetime technical support, this 2-port high-resolution VGA splitter lets you get the most out of your video content with quality construction you can depend on.

## Certifications, Reports and Compatibility

### Applications

- In-store product merchandising
- Information booths/kiosks
- Trade-shows
- Lecture halls and classrooms

- Airports, bus terminals and train stations

## Features

- Compatible with VGA, SVGA and Multisync monitors
- 400 MHz bandwidth provides brilliant 2048 x 1536 resolution
- DDC, DDC2 & DDC2B compatible (on Video Out port 1)
- Includes DC 7.5V power adapter
- Daisy chainable for almost unlimited expansion
- Uses standard monitor extension cables (StarTech.com coaxial VGA cables recommended for best picture quality)

---

### Hardware

Warranty	2 Years
Ports	2
AV Input	VGA
AV Output	VGA
Audio	Yes

---

### Performance

Maximum Analog Resolutions	2048x1536 @ 60Hz
Bandwidth	400MHz

---


### Connector(s)

Connector A	3.5 mm Mini-Jack (3 Position)
	VGA (15 pin, High Density D-Sub)
Connector B	3.5 mm Mini-Jack (3 Position)
	VGA (15 pin, High Density D-Sub)

---

### Special Notes / Requirements

Note	Units made before August 2008 shipped with AC 7.5V 800mA power adapter
------	--



---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	12V DC
Output Current	0.6A
Power Consumption (In Watts)	7.2

---

**Physical Characteristics**

Color	Gray
Product Length	5.1 in [13.0 cm]
Product Width	3.0 in [75.0 mm]
Product Height	2.8 in [72.0 mm]
Weight of Product	15.8 oz [447.0 g]

---

**Packaging Information**

Package Length	6.2 in [15.7 cm]
Package Width	9.6 in [24.4 cm]
Package Height	2.6 in [67.0 mm]
Shipping (Package) Weight	25.2 oz [715.0 g]

---

**What's in the Box**

Included in Package	2 Port VGA Splitter
	Power Adapter
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

