

2 Port High Resolution VGA Video Splitter with Audio - 400 MHz

Product ID: ST122PROA



This high resolution VGA splitter offers a practical solution for high-res multi-screen presentations, allowing a VGA video signal as well as the corresponding audio to be broadcast from a computer to up to two sets of VGA monitors and speakers simultaneously.

The VGA splitter is ideal for classrooms, tradeshow, in-store displays or any application where high quality video and audio is required, supporting displays with up to 400 MHz of video bandwidth and high resolution applications up to 2048 x 1536.

To help ensure high quality VGA video even at longer distances, the high resolution VGA splitter features a built-in booster circuit that allows monitors to be located up to 210ft away from the host system.

Designed for simplicity and convenience, the VGA splitter offers easy plug and play installation; a completely hardware-based solution, the VGA splitter requires no software operation, saving both time and hassle.

Backed by our 2-year warranty and free lifetime technical support, this 2-port high-resolution VGA splitter lets you get the most out of your video content with quality construction you can depend on.

Certifications, Reports and Compatibility



Applications

- In-store product merchandising
- Information booths/kiosks

- Trade-shows
- Lecture halls and classrooms
- Airports, bus terminals and train stations

Features

- Compatible with VGA, SVGA and Multisync monitors
- 400 MHz bandwidth provides brilliant 2048 x 1536 resolution
- DDC, DDC2 & DDC2B compatible (on Video Out port 1)
- Includes DC 7.5V power adapter
- Daisy chainable for almost unlimited expansion
- Uses standard monitor extension cables (StarTech.com coaxial VGA cables recommended for best picture quality)

Hardware

Warranty	2 Years
AV Input	VGA
Ports	2
AV Output	VGA
Audio	Yes

Performance

Maximum Analog Resolutions	2048x1536 @ 60Hz
Bandwidth	400MHz

Connector(s)

Connector A	1 - 3.5 mm Mini-Jack (3 Position)
	1 - VGA (15 pin, High Density D-Sub)
Connector B	2 - 3.5 mm Mini-Jack (3 Position)
	2 - VGA (15 pin, High Density D-Sub)

Special Notes /

Requirements

Note	Units made before August 2008 shipped with AC 7.5V 800mA power adapter
------	--

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	12V DC
Output Current	0.6A
Power Consumption (In Watts)	7.2

Physical Characteristics

Color	Gray
Product Length	5.1 in [13.0 cm]
Product Width	3.0 in [7.5 cm]
Product Height	2.8 in [7.2 cm]
Weight of Product	15.8 oz [447.0 g]

Packaging Information

Package Quantity	1
Package Length	6.2 in [15.7 cm]
Package Width	9.6 in [24.4 cm]
Package Height	2.6 in [6.7 cm]
Shipping (Package) Weight	1.6 lb [0.7 kg]

What's in the Box

Included in Package	1 - 2 Port VGA Splitter
	1 - Power Adapter
	1 - Instruction Manual

**Product appearance and specifications are subject to change without notice.*