

VGA Video extender mit Audio bis zu 150m und einer max. Auflösung von 1140x900

Produkt-ID: ST122UTPA



The ST122UTPA VGA Video Extender over Cat 5 with Audio allows up to 4 (2 local and 2 remote) monitors to be connected to a single PC. The video signal and corresponding audio are sent to the remote unit over standard 4 pair Category 5 or better (Cat 5e recommended) UTP cable, supporting extended video distances of up to 150m / 500ft.

The VGA video and audio extender includes a local transmitter and a remote receiver, providing an out-of-the box solution that's perfect for point to point digital signage applications that require audio. To simplify installation, this kit also includes a mounting bracket for the ST122UTPA receiver to install onto walls, desks or cabinets for a tidy setup.

This product is TAA compliant and backed by a Startech.com 2-year warranty with free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors

- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at tradeshowes and in auditoriums

Merkmale

- Consists of 1 Base unit for the local display, and 1 Remote unit for the remote display (up to 2 monitors can be connected at each location)
- Extends VGA and analog audio up to 500ft / 150m
- Included mounting brackets
- Pure hardware design, no software or drivers required
- Uses standard Category 5 straight-wired, twisted-pair, network patch cable for economical and reliable data transmission

Hardware

Garantiebestimmungen	2 Years
Ports	2
Kabel	Cat5e UTP oder höher
Audio	Ja
Reihenschaltung	Nein

Leistung

Max. Kabellänge	500.0 ft [152.4 m]
Max. Entfernung	150m [492ft]
Unterstützte Auflösungen	1440x900 @ 150ft / 50m 1280x1024 @ 300ft / 100m 1024x768 @ 500ft / 150m

Steckverbinder

Anschlüsse lokales Gerät	2 - 3,5 mm Mini-Jack (3 Positionen)
--------------------------	-------------------------------------

		1 - RJ-45
		2 - VGA (15-polig, High Density D-Sub)
		1 - VGA (15-polig, High Density D-Sub)
Remote-Gerät-Anschlüsse		2 - 3,5 mm Mini-Jack (3 Positionen)
		1 - RJ-45
		2 - VGA (15-polig, High Density D-Sub)
Strom		
	Stromversorgung	Mit Netzadapter
	Ausgangsspannung	12V DC
	Ausgangsstrom	0.5A
	Polarität der Mittelspitze	Positiv
	Stromverbrauch	6
Physische Eigenschaften		
	Farbe	Schwarz
	Gehäusotyp	Aluminium
	Produktlänge	2.4 in [6.0 cm]
	Produktbreite	3.3 in [8.3 cm]
	Produkthöhe	0.8 in [2.0 cm]
	Produktgewicht	14.2 oz [402.0 g]
Verpackungsinformationen		
	Paketmenge	1
	Paketlänge	9.5 in [24.2 cm]
	Paketbreite	7.3 in [18.6 cm]

Pakethöhe 3.6 in [9.2 cm]

Versandgewicht
(Verpackung) 2.2 lb [1.0 kg]

Verpackungsinhalt

Im Paket enthalten	1 - Local VGA Extender Unit
	1 - Remote VGA Extender Unit
	1 - Mounting Bracket Kit (w/ screws)
	2 - Sets Rubber Feet
	2 - Power Adapter
	1 - Instruction Manual

Garantieinformationen

Warranty	2 Jahre
----------	---------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.