

## VGA Video Extender over Cat 5 with Audio

**Product ID:** ST122UTPAEU



The ST122UTPAEU VGA Video Extender over Cat 5 with Audio allows up to 4 (2 local and 2 remote) monitors to be connected to a single PC. The video signal and corresponding audio are sent to the remote unit over standard 4 pair Category 5 or better (Cat 5e recommended) UTP cable, supporting extended video distances of up to 150m / 500ft.

The VGA video and audio extender includes a local transmitter and a remote receiver, providing an out-of-the box solution that's perfect for point to point digital signage applications that require audio. To simplify installation, this kit also includes a mounting bracket for the ST122UTPAEU receiver to install onto walls, desks or cabinets for a tidy setup.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings

- Optimize placement of your demo stations at tradeshow and in auditoriums

## Features

- Extends VGA and analog audio up to 500ft / 150m
- Supports 1440x900 resolution at 150 ft. (50m)
- Supports 1024x768 resolution at 500 ft. (150m)
- Consists of 1 Base unit for the local display, and 1 Remote unit for the remote display (up to 2 monitors can be connected at each location)
- Pure hardware design, no software or drivers required
- Uses standard Category 5 straight-wired, twisted-pair, network patch cable for economical and reliable data transmission
- Includes mounting brackets

---

### Hardware

Warranty	2 Years
Ports	2
Cabling	Cat 5e UTP or better
Daisy-Chain	No

---

### Performance

Maximum Cable Length	6001.6 in [152440 mm]
Max Distance	150m [492ft]
Maximum Analog Resolutions	Distance / Resolution 100ft (30m) / 1440x900 250ft (76m) / 1280x1024 500ft (152m) / 1024x768
Wide Screen Supported	Yes

---

### Connector(s)

Local Unit Connectors	3 - 3.5 mm Mini-Jack (3 Position) 1 - RJ-45
-----------------------	--

Remote Unit Connectors		2 - VGA (15 pin, High Density D-Sub)
		1 - VGA (15 pin, High Density D-Sub)
		2 - 3.5 mm Mini-Jack (3 Position)
		1 - RJ-45
		2 - VGA (15 pin, High Density D-Sub)
<b>Power</b>		
	Power Source	2 AC Adapters Included
	Center Tip Polarity	Positive
<b>Physical Characteristics</b>		
	Color	Black
	Material	Aluminum
	Product Length	0.0 in [0.0 mm]
	Product Width	0.0 in [0.0 cm]
	Product Height	0.0 in [0.0 cm]
	Weight of Product	6.4 oz [181.0 g]
<b>Packaging Information</b>		
	Package Quantity	1
	Package Length	9.5 in [24.2 cm]
	Package Width	3.6 in [92.0 mm]
	Package Height	7.4 in [18.8 cm]
	Shipping (Package) Weight	2.7 lb [1.2 kg]
<b>What's in the Box</b>		
	Included in Package	1 - Local Unit (Transmitter)
		1 - Remote Unit (Receiver)
		1 - Mounting Bracket for Receiver (w/ screws)

2 - Sets Rubber Feet

2 - Power Adapters

1 - Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***