

VGA Video Extender over Cat 5 with Audio

Product ID: ST122UTPAEU



The ST122UTPAEU VGA Video Extender over Cat 5 with Audio allows up to 4 (2 local and 2 remote) monitors to be connected to a single PC. The video signal and corresponding audio are sent to the remote unit over standard 4 pair Category 5 or better (Cat 5e recommended) UTP cable, supporting extended video distances of up to 150m / 500ft.

The VGA video and audio extender includes a local transmitter and a remote receiver, providing an out-of-the box solution that's perfect for point to point digital signage applications that require audio. To simplify installation, this kit also includes a mounting bracket for the ST122UTPAEU receiver to install onto walls, desks or cabinets for a tidy setup.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at tradeshow and in auditoriums

Features

- Consists of 1 Base unit for the local display, and 1 Remote unit for the remote display (up to 2 monitors can be connected at each location)
- Extends VGA and analog audio up to 500ft / 150m
- Pure hardware design, no software or drivers required
- Includes mounting brackets
- Uses standard Category 5 straight-wired, twisted-pair, network patch cable for economical and reliable data transmission
- Supports 1440x900 resolution at 150 ft. (50m)
- Supports 1024x768 resolution at 500 ft. (150m)

Hardware

Warranty	2 Years
Ports	2
Cabling	Cat 5e UTP or better
Daisy-Chain	No

Performance

Maximum Cable Length	500.0 ft [152.4 m]
Max Distance	150 m / 500 ft
Maximum Analog Resolutions	Distance / Resolution 100ft (30m) / 1440x900 250ft (76m) / 1280x1024 500ft (152m) / 1024x768
Wide Screen Supported	Yes

Connector(s)

Local Unit Connectors	VGA (15 pin, High Density D-Sub)
	VGA (15 pin, High Density D-Sub)
	RJ-45
	3.5 mm Mini-Jack (3 Position)



Remote Unit Connectors VGA (15 pin, High Density D-Sub)

RJ-45

3.5 mm Mini-Jack (3 Position)

Power

Power Source 2 AC Adapters Included

Center Tip Polarity Positive

Physical Characteristics

Color Black

Material Aluminum

Product Length 0.0 in [0.0 mm]

Product Width 0.0 in [0.0 mm]

Product Height 0.0 in [0.0 mm]

Weight of Product 6.4 oz [181.0 g]

Packaging Information

Package Length 9.5 in [24.2 cm]

Package Width 3.6 in [92.0 mm]

Package Height 7.4 in [18.8 cm]

Shipping (Package) Weight 2.7 lb [1.2 kg]

What's in the Box

Included in Package

- Power Adapters
- Instruction Manual
- Local Unit (Transmitter)
- Remote Unit (Receiver)
- Mounting Bracket for Receiver (w/ screws)
- Sets Rubber Feet

****Product appearance and specifications are subject to change without notice.***

