

## VGA Video Extender over Cat 5 with Audio

**Product ID:** ST122UTPAGB



The ST122UTPAGB VGA Video Extender over Cat 5 with Audio allows up to 4 (2 local and 2 remote) monitors to be connected to a single PC. The video signal and corresponding audio are sent to the remote unit over standard 4 pair Category 5 or better (Cat 5e recommended) UTP cable, supporting extended video distances of up to 150m / 500ft.

The VGA video and audio extender includes a local transmitter and a remote receiver, providing an out-of-the box solution that's perfect for point to point digital signage applications that require audio. To simplify installation, this kit also includes a mounting bracket for the ST122UTGB receiver to install onto walls, desks or cabinets for a tidy setup.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Place the display in a convenient viewing area, while the system equipment is placed elsewhere in a clean and secure environment
- Ideal for digital signage applications in financial, educational, and business sectors
- Extend your display across harsh environment industrial sites
- Perfect for video conferencing solutions in boardrooms and office settings
- Optimize placement of your demo stations at tradeshow and in auditoriums

## Features

- Consists of 1 Base unit for the local display, and 1 Remote unit for the remote display (up to 2 monitors can be connected at each location)
- Extends VGA and analog audio up to 500ft / 150m
- Uses standard Category 5 straight-wired, twisted-pair, network patch cable for economical and reliable data transmission
- Pure hardware design, no software or drivers required

---

### Hardware

Warranty	2 Years
Cabling	Cat 5e UTP or better
Daisy-Chain	No

---

### Performance

Max Distance	150m [492ft]
Supported Resolutions	1440x900 @ 150ft / 50m 1280x1024 @ 300ft / 100m 1024x768 @ 500ft / 150m

---

### Connector(s)

Local Unit Connectors	3 - 3.5 mm Mini-Jack (3 Position)
	1 - RJ-45
	1 - VGA (15 pin, High Density D-Sub)
	2 - VGA (15 pin, High Density D-Sub)
Remote Unit Connectors	1 - 3.5 mm Mini-Jack (3 Position)
	1 - RJ-45
	2 - VGA (15 pin, High Density D-Sub)

---

### Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC

Input Current	0.2 A
Output Voltage	9V DC
Output Current	0.6 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	5.4

---

#### Physical Characteristics

Color	Black
Material	Aluminum
Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	14.2 oz [402.0 g]

---

#### Packaging Information

Package Quantity	1
Package Length	9.5 in [24.2 cm]
Package Width	3.6 in [9.2 cm]
Package Height	7.4 in [18.8 cm]
Shipping (Package) Weight	2.7 lb [1.2 kg]

---

#### What's in the Box

Included in Package	1 - Local VGA Extender Unit
	1 - Remote VGA Extender Unit
	1 - Mounting Bracket Kit (w/ screws)
	2 - Sets Rubber Feet

2 - Power Adapter

1 - Instruction Manual

---

**Warranty  
Information**

Warranty

2 Years

---

*\*Product appearance and specifications are subject to change without notice.*