

2 Port Wall Mount VGA Video Splitter

Product ID: ST122WGB



The ST122WGB 2 Port wall-mountable VGA Video Splitter offers outstanding quality and distance, allowing you to deliver high resolution VGA video from a single video source to up to two monitors simultaneously.

Supporting a maximum VGA video bandwidth of up to 250MHz and resolutions up to 1600 x 1200, the device is sure to deliver on image quality. The wall-mountable multi-display VGA video splitter is very simple to install, allowing you to locate screens up to 65m (210ft) away from the VGA video source.

The video splitter provides versatile installation options, with top-side connection ports the unit can lay flat on or under your workspace, or you have the option to mount the splitter on a wall making it easy to position the VGA splitter as needed. A scalable video splitting solution, the device also allows you to cascade the signal using two additional splitters for broadcast from a single VGA source to up to 8 VGA monitors.

Typical applications of this product would include digital signage, retail and tradeshow environments, educational and government facilities, or corporate displays where high quality multi-monitor VGA video is required.

Backed by a StarTech.com 2-year warranty and free lifetime technical support., Male to Female VGA extension cable required (MXT101HQ)

Certifications, Reports and Compatibility



Applications

- Use for in-store product merchandising in retail environments to give your advertisements greater visibility

- Display travel schedules and alerts in airports, bus terminals and train stations
- Create engaging multimedia presentations for demonstration in lecture halls and classrooms
- Get your message across multiple displays for trade-shows or information booths/kiosks
- Quick and easy solution to split a video signal in an auditorium or house of worship

Features

- Compact design with convenient topside connection
- Lays flat or mounts on the wall
- Supports resolutions up to 1600x1200
- Supports cable distances up to 210ft
- 250MHz video bandwidth
- Supports Cascading up to 3 levels

Hardware

Warranty	2 Years
AV Input	VGA
Ports	2
AV Output	VGA

Performance

Maximum Cable Length	213.2 ft [65 m]
Maximum Analog Resolutions	1600x1200 @ 75Hz
Bandwidth	250MHz
General Specifications	Male to Female VGA extension cable required (MXT101HQ)

Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	2 - VGA (15 pin, High Density D-Sub)

Power

Power Source	AC Adapter Included
--------------	---------------------

Input Voltage	100 - 240 AC
Input Current	0.2 A
Output Voltage	9V DC
Output Current	0.6 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	5.4

Environmental

Operating Temperature	0 ~ 50 C
Storage Temperature	-20 ~ 60 C

Physical Characteristics

Color	Silver
Material	Plastic
Product Length	0.3 in [8.8 mm]
Product Width	0.1 in [0.2 cm]
Product Height	0.2 in [0.6 cm]

Packaging Information

Package Quantity	1
Package Length	9.4 in [24 cm]
Package Width	2.3 in [59 mm]
Package Height	6.4 in [16.2 cm]
Shipping (Package) Weight	0.9 lb [0.4 kg]

What's in the Box

Included in Package	1 - 2 Port VGA Splitter
---------------------	-------------------------

1 - Power Adapter

1 - Instruction Manual

**Warranty
Information**

Warranty

2 Years

**Product appearance and specifications are subject to change without notice.*