

4K HDMI Splitter - HDMI Splitter 1 In 4 Out - 4-Port - 4K 60Hz

Product ID: ST124HD20



This 4K HDMI splitter lets you connect your HDMI video source to four HDMI displays, with support for Ultra HD resolutions and HDR (High Dynamic Range) as well as 7.1 surround sound audio.

Unlike many 4K splitters that only support a 30Hz refresh rate, this splitter works with 4K HDMI 2.0 displays with output resolutions of up to 3840 x 2160p at 60Hz.

Not all 4K splitters are created equal. While some HDMI 1.4 splitters can achieve 4K resolutions, they'll only work at a 30Hz refresh rate. Other HDMI 1.4 splitters are marketed as 4K at 60Hz, but their color data is reduced to a lower 4:2:0 chroma subsampling. This drastically reduces color quality in order to achieve 4K at 60Hz resolution, even with limited HDMI 1.4 bitrate capabilities.

This 4K 60Hz HDMI splitter offers full support for your HDMI 2.0 equipment, including true 4K resolution at 60Hz. For smoother video and color transitions, the splitter offers 4:4:4 chroma subsampling, meaning every pixel gets its own unique color. Support for HDMI 2.0 devices means this splitter can transmit bandwidth up to 18Gbps, making it the ideal solution for high-resolution tasks requiring the highest color detail.

The splitter supports HDCP 2.2 and is backward compatible with 4K 30Hz and 1080p displays. This ensures that it will work with lower resolution displays such as TVs or projectors around your site or in your digital signage application.

For hassle-free setup, the 4K HDMI splitter offers easy plug-and-play installation with no additional software or drivers required. The splitter passes EDID between your video source and the display attached to port 1, ensuring native settings such as resolution and refresh rate are configured automatically.

The ST124HD20 is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Output and split your 4K 60Hz HDMI signal to four different HDMI displays
- Distribute 4K60 video to computer monitors that require the highest quality of image detail, such as in control centers or video production studios
- Display corporate information or advertising on multiple displays at a shopping center
- Display the same information on multiple displays in the waiting rooms of healthcare facilities

Features

- Astonishing picture quality with support for 4K 60Hz and HDR
- Support for 7.1 surround sound audio
- Supports 4:4:4 chroma subsampling even at 4K 60Hz with bandwidth up to 18Gbps

Hardware

Warranty	2 Years
AV Input	HDMI
Ports	4
AV Output	HDMI
Audio	Yes
Industry Standards	HDMI 2.0

Performance

Maximum Analog Resolutions	4K @ 60Hz
Maximum Digital Resolutions	3840x2160 (4K) @ 60Hz
	2560x1600
	1920x1200
	1920x1080 (1080p)

		1280x720 (720p)
	Wide Screen Supported	Yes
	Audio Specifications	7.1 surround sound
Connector(s)		
	Connector A	1 - HDMI (19 pin)
	Connector B	4 - HDMI (19 pin)
Special Notes / Requirements		
	Note	This video splitter is not compatible with the AMD Radeon RX460 graphics card
Indicators		
	LED Indicators	1 - power LED
		1 - input LED
		4 - output LEDs
Power		
	Input Voltage	100 - 240 AC
	Input Current	0.35 A
	Output Voltage	5 DC
	Output Current	2 A
Environmental		
	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	20~90 % RH (non-condensing)
Physical Characteristics		
	Color	Black
	Product Length	6.3 in [16.1 cm]
	Product Width	2.5 in [6.3 cm]
	Product Height	0.7 in [1.7 cm]

Weight of Product	9.6 oz [271.0 g]
-------------------	------------------

Packaging Information

Package Quantity	1
Package Length	8.3 in [21.2 cm]
Package Width	5.8 in [14.8 cm]
Package Height	2.2 in [55.0 mm]
Shipping (Package) Weight	0.2 lb [0.1 kg]

What's in the Box

Included in Package	1 - HDMI video splitter
	1 - universal power adapter (NA, EU, UK, ANZ)
	1 - quick-start guide

****Product appearance and specifications are subject to change without notice.***