

8 Port VGA Video Splitter - Wall Mountable

Product ID: ST128W



This 8 Port wall-mountable VGA Video Splitter offers outstanding quality and distance, allowing you to deliver high resolution VGA video from a single video source to up to eight monitors simultaneously.

The wall-mountable multi-display VGA video splitter is very simple to install, allowing you to locate screens up to 200ft away from the VGA video source, supporting a maximum VGA video bandwidth of up to 200MHz while delivering display resolutions up to 1600 x 1200.

The video splitter provides versatile installation options, with top-side connection ports as well as the option to mount the splitter on a wall, making it easy to position the VGA splitter as needed.

The VGA video splitter offers a scalable video splitting solution, allowing you to cascade the VGA signal using additional splitters for broadcast from a single VGA source to up to 512 VGA monitors.

Typical applications of this product would include digital signage, retail and tradeshow environments, educational and government facilities, or corporate displays where high quality, multi-monitor VGA video is required.

StarTech.com's 8 Port wall-mountable VGA Video Splitter is backed by our 2-year warranty and includes free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Airports, bus terminals and train stations

- In-store product merchandising
- Information booths/kiosks
- Lecture halls and classrooms
- Trade-shows

Features

- Max resolutions up to 1600 x 1200
- Cascadable up to 3 levels and provides up to 512 video signals
- Compact design with convenient topside connection, lays flat or mounts on the wall
- Supports distances up to 65m / 200ft

Hardware

Warranty	2 Years
Ports	8

Performance

Maximum Cable Length	213.2 ft [65 m]
Maximum Analog Resolutions	1600x1200
Bandwidth	200MHz

Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	8 - VGA (15 pin, High Density D-Sub)

Power

Output Voltage	9V DC
Output Current	0.3A
Center Tip Polarity	Positive

Environmental

Operating Temperature	0C to 50C (32F to 122F)
-----------------------	-------------------------

Storage Temperature -20C to 60C (-4F to 140F)

Physical Characteristics

Color	Silver
Material	Plastic
Product Length	0.0 in [0.0 mm]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	0.0 oz [0.0 g]

Packaging Information

Package Length	9.4 in [24.0 cm]
Package Width	2.3 in [5.9 cm]
Package Height	6.4 in [16.2 cm]
Shipping (Package) Weight	1.3 lb [0.6 kg]

What's in the Box

Included in Package	1 - 8 Port Video Splitter
	1 - Power Adapter
	1 - Instruction Manual

Warranty Information

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*