

HDMI to CAT5 Repeater for ST12MHDDC – 1080p / 1920x1080

Produkt ID: ST12MHDDCRP



The ST12MHDDCRP HDMI® to CAT5 Repeater works with the ST12MHDDC HDMI Extender Kit to add additional displays and extend the HDMI over Cat 5/6 signal. With 2 RJ45 outputs per unit, each repeater allows you to add a display, and also daisy-chain the signal to 2 additional ST12MHDDCRP repeaters (sold separately) at up to 330 feet (100 meters) at each level.

Additional repeaters can be added at any time, up to a maximum of 30 broadcasting levels to over 100 displays, allowing for a highly scalable installation that can be used with existing network cable for a cost-effective and flexible extension. Plus, because the HDMI signal is extended over standard Cat5/Cat6 Ethernet cable with RJ45 connectors, proprietary cables aren't necessary which eliminates both expense and the hassle of running specialized cable.

Ideal for High-Definition applications, the HDMI over UTP extender supports 1080p video resolutions, 7.1 digital audio and features built-in EDID monitor emulation, which ensures native resolution and maximum compatibility with your display or projector, for a convenient plug-and-play installation.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Optimize placement of your demo stations at tradeshows and in auditoriums

- Perfect for video conferencing solutions in boardrooms and office settings
- Place the display in a convenient viewing area, while the HDMI source equipment is placed elsewhere in a separate, secured environment
- Display the same HDMI audio/video signal on up to 100 displays, for large scale digital signage applications

Funktioner

- 2 RJ45 output ports, for additional Daisy-chain support
- High Definition support for resolutions up to 1080p (1920x1080)
- EDID emulation ensures maximum resolution and compatibility with your display or projector
- Supports a maximum HDMI extension of 330ft (100m)
- 7.1 Surround Sound Audio Support

Hårdvara

Garantipolicy	2 Years
Portar	1
Kablage	Cat 5 UTP
Audio	Ja
Hyllmonterbar	Ja
Kedjekoppling	Ja

Prestanda

Maximalt avstånd	100m [328ft]
Maximal digital upplösning	1920x1200 @60Hz
Stödda upplösningar	1920 x 1200
	1920 x 1080
	1600 x 1200
Stöd för widescreen	Ja

Audio-specifikationer 7.1 Surround Sound

Kontakt(er)

Lokala enhetskontakter 1 - HDMI (19-stifts)

Fjärrenhetskontakter 2 - RJ-45

Indikatorer

LED-indikatorer 1 - Power (Red)

1 - Status (Green)

Ström

Strömkälla AC-adapter medföljer

Inspänning 100 - 240 AC

Inström 0.4 A

Utspanning 5 DC

Utström 2 A

Polaritet på mittpol Positiv

Kontakttyp M

Miljö

Drifttemperatur 0°C to 40°C (32°F to 104°F)

Förvaringstemperatur -10°C to 60°C (14°F to 140°F)

Luftfuktighet 0% - 80 %

Utseende

Färg Svart

Kabinettyp Aluminium och plast

Produktlängd 5.0 in [12.8 cm]

Produktbredd 3.0 in [7.5 cm]

Produkthöjd 0.9 in [2.4 cm]

	Produktvikt	11.0 oz [313 g]
Förpackning		
	Förpackningsantal	1
	Paketets längd	6.6 in [16.8 cm]
	Paketets bredd	5.6 in [14.3 cm]
	Paketets höjd	2.5 in [63 mm]
	Fraktvikt (förpackning)	1.3 lb [0.6 kg]
Vad det är i lådan		
	Ingår i paketet	1 - HDMI Repeater
		1 - Foot Pad Set
		2 - Power Adapter
		1 - Instruction Manual
Warranty Information		
	Warranty	2 År

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.