

4 Port Compact Black USB 2.0 Hub

Product ID: ST4202USB



This TAA compliant 4 Port USB 2.0 Hub connects to one USB 2.0 port on a Mac or PC computer, adding four USB 2.0 ports - allowing you to maximize the number of high speed USB peripherals connected to your computer. The hub supports cascaded installation with other USB 2.0 hubs, supporting up to 127 USB 2.0 device connections - a scalable solution for connecting multiple USB devices to a single host computer.

The 4 port hub includes a power adapter, but can be powered through USB bus connection to the host computer - allowing you to install the hub as needed without worrying about the availability of a power outlet.

The USB 2.0 hub offers an attractive black casing that suits any operating environment and includes a 3ft USB 2.0 A/B male-male cable, for the connection between the hub and the host computer.

Certifications, Reports and Compatibility

Applications

- Charge iPod's or other portable devices that can be recharged through USB 2.0
- Add additional USB 2.0 ports to a computer to connect more devices
- Move USB ports further away from the computer chassis with an external hub
- Make hard to reach USB ports more accessible, by being able to position the hub anywhere the cable will reach

Features

- TAA Compliant

- High Speed USB 2.0 compliant, with supported data transfer rates up to 480 Mbps
- Backwards compatible with USB 1.1/1.0 devices
- Includes optional external power adapter
- Compact and light-weight design
- Plug and Play and Hot Swap compatible

Hardware

Warranty	2 Years
Ports	4
Interface	USB 2.0
Industry Standards	USB 2.0
Chipset ID	Genesys Logic - GL850G

Performance

Maximum Data Transfer Rate	480 Mbps
MTBF	75,537 hours

Connector(s)

External Ports	USB Type-A (4 pin) USB 2.0 USB B (4 pin)
----------------	---

Software

OS Compatibility	OS Independent; No software or drivers required. (For Apple, Mac OS 10.2.4 needed for USB 2.0 speeds)
------------------	---

Special Notes / Requirements

System and Cable Requirements	Any computer with a USB 2.0 port
-------------------------------	----------------------------------

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.35 A



Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	H
Power Consumption (In Watts)	10

Environmental

Operating Temperature	0 to 70 Degrees C
-----------------------	-------------------

Physical Characteristics

Color	Black
Material	Plastic
Product Length	3.9 in [100.0 mm]
Product Width	2.4 in [60.0 mm]
Product Height	0.8 in [20.0 mm]
Weight of Product	2.5 oz [71.0 g]

Packaging Information

Package Length	8.3 in [21.0 cm]
Package Width	5.7 in [14.5 cm]
Package Height	1.6 in [40.0 mm]
Shipping (Package) Weight	10.2 oz [290.0 g]

What's in the Box

Included in Package	4 Port USB 2.0 Hub
	USB Cable
	Power Adapter
	Instruction Manual



****Product appearance and specifications are subject to change without notice.***

