

4 Port Black SuperSpeed USB 3.0 Hub

Product ID: ST4300USB3GB



The ST4300USB3GB 4-Port SuperSpeed USB 3.0 Hub allows you to add 4 additional USB 3.0 ports from a single USB 3.0 connection to the host computer system.

Backward compatible with USB 2.0 and USB 1.x standards, this USB 3.0 hub still supports older USB devices and can also be used as a hub on older systems that do not have USB 3.0 ports.

With the capability to mix and match USB 3.0/2.0/1.x devices and be used with or without the included external power adapter, this hub offers the best of versatility and portability.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Expand your USB 3.0 capabilities with additional ports
- Make hard to access USB ports more accessible by being able to position the hub anywhere the cable will reach
- Extend the range of a USB device by having the hub act as a mid-point repeater

Features

- Four USB type 'A' ports that can each be accessed simultaneously
- SuperSpeed USB 3.0 compliant, with data transfer rates up to 5 Gbps

- Backward compatible with USB 2.0 and USB 1.0/1.1 devices
- Supports USB 3.0/2.0/1.x devices simultaneously at full bandwidth
- Provides up to 900mA on any port up to a maximum of 2000mA total
- Compact, desktop-style form factor
- Plug-and-Play and hot-swap compatible

Hardware

Warranty	2 Years
USB-C Device Port(s)	No
USB-C Host Connection	No
Fast-Charge Port(s)	No
Ports	4
Interface	USB 3.0
Bus Type	USB 3.0
	USB 3.0
Chipset ID	VIA/VLI - VL811+

Performance

Total USB Power Output	10W
Maximum Data Transfer Rate	5 Gbps

Connector(s)

External Ports	USB Type-A (9 pin) USB 3.0 (5 Gbps)
	USB Type-B (9 pin) USB 3.0

Software

OS Compatibility	OS Independent; No additional drivers or software required
------------------	--

Special Notes / Requirements

System and Cable Requirements	USB 3.0 or 2.0 or 1.x compliant host controller with available port.
-------------------------------	--

Indicators

LED Indicators Power (Blue)

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	10

Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	5~85% RH

Physical Characteristics

Color	Black
Form Factor	Desktop
Material	Plastic
Product Length	3.7 in [95 mm]
Product Width	2.7 in [68 mm]
Product Height	0.9 in [23 mm]
Weight of Product	1.9 oz [55 g]

Packaging Information

Package Length	8.3 in [21 cm]
Package Width	5.9 in [15 cm]
Package Height	3.1 in [80 mm]



Shipping (Package) Weight	15.5 oz [440 g]
------------------------------	-----------------

What's in the Box

Included in Package	USB 3.0 Hub
	USB 3.0 cable
	Power Adapter
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

