

## TV Cart - Height Adjustable - Lockable Wheels

**Product ID:** STNDMTV70



This portable TV cart makes it easy to create a mobile media center, providing a convenient and cost-effective way to share A/V equipment between rooms. Engineered with a sleek and sturdy design, the TV cart provides a secure mount for a 32" to 75" TV (with maximum weight of 88 lb./40 kg) and a removable multi-media shelf for placing your computer, media player or keyboard. It also includes a camera shelf for web-conferencing.

The mobile TV cart saves you the cost of buying multiple flat-panel TVs. Simply roll the TV cart between boardrooms, classrooms and meeting rooms, to share your media equipment. The cart features a small footprint that enables you to stand close to the display, while delivering a presentation. You can also set up a display in your lobby during special events or set up a permanent display in areas where you can't wall mount. The wheels are lockable for stationary use.

With the TV cart's spring-assisted height adjustment, you can raise or lower the display mount with one smooth motion, from a minimum height of 3.6 ft. (1110 mm) to a maximum height of 4.9 ft. (1510 mm) - a lift of up to 15.7 in. (40 cm). The TV mount rotates up to 90 degrees, so you can change the position of your display from landscape to portrait. You can also tilt your TV +5 to -12 degrees, to find the optimal viewing angle.

The TV cart's durable construction makes it ideal for commercial use, in environments with multiple users and frequent movement between meeting areas. Built-in cable management keeps your cables organized and hidden from view.

The STNDMTV70 is backed by a StarTech.com 5-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Roll the cart between boardrooms, classrooms or other spaces

- Share media equipment and minimize costs
- Set up a stationary display during special events
- Set up a permanent display in areas where you can't wall mount

## Features

- Easily share displays between rooms, by mounting a 32" to 75" flat-screen TV to this mobile TV cart
- Smooth spring-assisted height adjustment up to 15.7" (400 mm)
- TV mount tilts +5 to -12 degrees for optimal viewing, and rotates from landscape to portrait
- Multimedia device shelf for web conferencing and other applications
- Wheels for easy mobility, also lockable for safety

---

### Hardware

Warranty	5 Years
# of Displays Supported	1
Mounting Options	Mobile Cart
VESA Hole Pattern(s)	200x200 mm
	300x300 mm
	400x200 mm
	400x400 mm
	600x400 mm

---

### Performance

Weight Capacity (Per Display)	88.4 lb [40 kg]
Lift Capacity (per Display)	55.2 lb [25 kg]
Minimum Display Size	32"
Maximum Display Size	75"
Fits Curved Display	Yes
Video Wall	No



Height Adjustment	Yes
Minimum Height	3.6 ft [1.1 m]
Maximum Height	5.0 ft [1.5 m]
Display Tilt	+5 / -12
Display Rotation	+90 / - 90
Anti-theft	No

---

### Special Notes / Requirements

Note	The TV cart supports TVs weighing up to 88 lb. (40 kg). <br / >The TV cart also provides smooth spring-assisted height adjustment to make it effortless to change the height of the TV, along the column, for TVs weighing up to 55 lb. (25 kg). <br / >For TVs with a weight greater than 55 lb. (25 kg), additional manual effort will be required to reposition the TV along the column.
------	---

---

### Physical Characteristics

Color	Black & Silver
Material	Steel
Product Length	27.6 in [70 cm]
Product Width	32.6 in [82.8 cm]
Product Height	7.0 ft [2.1 m]
Weight of Product	70.2 lb [31.8 kg]

---


### Packaging Information

Package Length	5.6 ft [1.7 m]
Package Width	21.7 in [55.1 cm]
Package Height	9.5 in [24.1 cm]
Shipping (Package) Weight	70.2 lb [31.8 kg]

---

### What's in the Box

Included in Package	base
---------------------	------



left leg

right leg

left base cover

right base cover

left support bracket

right support bracket

column cover

column

multimedia shelf

camera shelf

connecting plate

plastic cover

cable clips

crossbars

wrench

hook and loop ties

end caps

adapter brackets

support plate

M6x16 mm screws

M6x25 mm screws

support plate nuts

countersunk screws

M4x6 mm screws

M6x8 mm screws

M6x14 mm screws



M8x25 mm screws

hex key

caster wrench

M5x14 mm screws

M6x14 mm screws

M8x50 mm screws

M6x30 mm screws

M8x30 mm screws

washers

small spacers

large spacers

instruction manual

shelf spacers

TV washers

---

***\*Product appearance and specifications are subject to change without notice.***

