

Dual TV Cart for 37-60in VESA TVs up to 110lb/50kg each - Height Adjustable TV Mount, Mobile Display Cart w/ Equipment Shelves - Rolling TV Cart on Wheels - Rolling TV Stand

Product ID: STNDMTVDUO



This Dual Mobile TV Stand enables you to create a rolling AV media center that is easy to move across classrooms, offices, boardrooms, meetings, or learning environments. For better stability and safety, the mobile cart was engineered with a large 1.22m x 0.71m base that will let you can mount two displays of 37" to 60" and up to 110lb/each in weight.

This mobile TV stand with mount will adapt to the different setups that you may encounter in your office space. You can adjust the height of your display from 1.2m to 1.68m from the center of the TV to the floor, and the included adjustment indicators allow you to perform precise adjustments for the ideal viewing height. Additionally, the height adjustment indicators make installation easier and enable you to note the preferred height for specific environments. You can also individually tilt the viewing angle within +5/-10 to best suit your environment and reduce glare. The included lockable casters allow to easily move the TV stand between locations.

For increased portability and customization, this universal mobile cart offers two independently adjustable device shelves (webcam shelf and equipment shelf) that each support up to 11lb/5kg. The webcam shelf can be raised up to 2.37m, while the equipment shelf can be raised up to 0.72m from the floor.

The heavy-duty dual TV stand's durable construction makes it ideal for commercial use, in environments with multiple users and frequent movement between areas. Built-in cable management keeps your cables organized and hidden from view.

The STNDMTVDUO is backed for 2-years by StarTech.com, including free lifetime 24/5 multi-lingual technical assistance.

Certifications, Reports and Compatibility

Applications

Features

- **DUAL TV CART:** Heavy duty aluminum mobile TV stand on wheels for 37-60 inch TVs & up to 110lb (50kg) per display; 4 lockable casters; Easily moved with attached handles; Sturdy steel base to prevent tipping hazard (48"x27.9"/1220mmx710mm)
- **EASILY ADJUSTABLE:** Synchronized display height adjustment range of 19" (0.5m); Adjustable height of 47.2"-66.4" (1.2m-1.7m) from center of TV to floor; Height indicators for precise adjustment; Each display tilts +5/-10
- **EQUIPMENT SHELVES:** 2 media shelves support 11lb/5kg (each) with height adjustability independent of each other & the display; Webcam shelf can be raised up to 93.5" (2.4m) & the lower media equipment shelf can be raised up to 28.3" (0.72m) from the floor
- **DISPLAY COMPATIBILITY:** Universal LCD/LED television mount for flat screens from brands like LG/Samsung/Sony/Sharp; For VESA patterns 200x200, 200x300, 200x400, 300x200, 300x300, 400x200, 400x300,400x400, 600x200, 600x300, 600x400; Screws/spacers included
- **MOBILE PRESENTATION CART:** Rolling TV stand/trolley with dual display for collaboration/meetings, shared across boardrooms, classrooms, etc; Cable management on floor standing TV mount w/ casters keeps cables organized for easy movement

Hardware

Warranty	2 Years
# of Displays Supported	2
Mounting Options	Mobile Cart
VESA Hole Pattern(s)	200x200 mm
	200x300 mm
	200x400 mm
	300x200 mm
	300x300 mm
	400x200 mm
	400x300 mm
	400x400 mm
	600X200 mm
	600x300 mm

600x400 mm

Performance

Minimum Display Size	37"
Maximum Display Size	60"
Fits Curved Display	Yes
Video Wall	No
Height Adjustment	Yes
Minimum Height	47.2 in [1200 mm]
Maximum Height	66.3 in [1685 mm]
Display Tilt	+ 5 / - 10
Anti-theft	No

Physical Characteristics

Product Length	28.0 in [71.0 cm]
Product Width	87.4 in [222.0 cm]
Product Height	93.5 in [237.5 cm]
Weight of Product	82.7 lb [37.5 kg]

Packaging Information

Package Quantity	1
Package Length	32.3 in [82.0 cm]
Package Width	4.3 ft [1.3 m]
Package Height	7.5 in [19.0 cm]
Shipping (Package) Weight	97.0 lb [44.0 kg]

What's in the Box

Included in Package	1 - Base
	4 - Casters

- 2 - Universal plates
- 2 - Handles
- 1 - Column, left
- 1 - Column, right
- 2 - Adapter brackets, left
- 2 - Adapter brackets, right
- 2 - Top covers
- 2 - Connectors
- 1 - DVD shelf
- 1 - Connector plate
- 1 - Camera shelf
- 2 - Fixing plates
- 1 - Support bar
- 2 - Knobs
- 4 - M6x15mm screws
- 2 - M6x25mm screws (button head)
- 2 - M6x25mm screws
- 3 - M4x6mm screws (flat head)
- 2 - M4x6mm screws
- 2 - M6x25mm screws (hex head)
- 10 - M6x14mm screws
- 8 - M8x25mm screws
- 2 - M6x25mm screws (carriage)
- 2 - Spacers
- 2 - Washers (round)
- 1 - Hex key

- 1 - Wrench
- 8 - M5x14mm screws
- 8 - M6x14mm screws
- 8 - M6x30mm screws
- 8 - M8x30mm screws
- 8 - M8x50mm screws
- 8 - Washers (rectangular)
- 16 - Spacers, small
- 16 - Spacers, big
- 1 - Manual

****Product appearance and specifications are subject to change without notice.***