

VGA Wall Plate Video Extender Transmitter over Cat 5 with Audio

Product ID: STUTPTXWLA



This CAT5 VGA Extender (Transmitter) Audio/Video Wall Plate can be used with StarTech.com's UTPEA VGA with Audio extender system, allowing in-wall connections from a VGA video and audio source to a remote location up to 300m (950ft) away.

Both VGA transmitter and Transmitter units use a 12V DC terminal block connector behind the unit that offers a more secure and economical installation; using Cat5/Cat6 cable to extend the VGA signal offers a cost-effective solution based on the broad availability of networking cable which is far more flexible than VGA cable, not to mention less expensive.

Unlike some video extension systems, our VGA extender wall plates also allow you to make use of an existing networking cable (Cat5, Cat6) infrastructure, eliminating the need to re-run cable in the event of an upgrade from VGA to another video standard, by simply swapping out the wall plates.

Certifications, Reports and Compatibility

Applications

- Ideal for applications in:
Education
Corporate
Digital Signage
Healthcare
Hospitality and Entertainment
Houses of Worship
- Ideal for Pro A/V installers and integrators looking for an easy solution to extend VGA video using Cat5 cabling.

Features

- Compatible with the UTPEA series VGA video extender receiver (STUTPEALR), also works with the wall plate VGA video extender receiver (STUTPRXWLA)

- Maximum VGA video and audio extension up to 300m/950ft (See Specifications for resolutions supported at various distances)
- Powered by terminal block connection
- Uses cost-effective Cat5 cable to extend VGA video and audio

Hardware

Warranty	2 Years
Ports	1
Cabling	Cat 5 UTP
Daisy-Chain	No

Performance

Max Distance	300 m / 950 ft
Supported Resolutions	1920x1200 @ 50m(164ft) 1600x1200 @ 100m(328ft) 1280x1024 @ 180m(590ft) 1024x768 @ 200m(656ft) 800x600 @ 300m(984ft)

Connector(s)

Local Unit Connectors	3.5 mm Mini-Jack (3 Position) RJ-45 Terminal Block (2 Wire) VGA (15 pin, High Density D-Sub)
-----------------------	---

Indicators

LED Indicators	Power LED
----------------	-----------

Power

Power Source	AC Adapter Included
Output Voltage	12V DC
Output Current	0.6A



Physical Characteristics

Color	White
Material	Steel
Product Length	4.1 in [10.5 cm]
Product Width	1.7 in [42 mm]
Product Height	1.5 in [38 mm]
Weight of Product	4.8 oz [136 g]

Packaging Information

Package Length	8.6 in [21.8 cm]
Package Width	2.8 in [71 mm]
Package Height	7.0 in [17.8 cm]
Shipping (Package) Weight	30.4 oz [860 g]

What's in the Box

Included in Package	VGA Video Extender Wall Plate Receiver
	Terminal Block for Power Adapter
	Power Adapter
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

