

1 Port USB PS/2 Server Remote Control IP KVM Switch with Virtual Media

Produkt ID: SV1108IPEXEU



The SV1108IPEXEU 1 Port USB PS/2 Server Remote Control IP KVM Switch with Virtual Media lets you control a USB or PS/2 server remotely over a LAN or the Internet.

The 1 port KVM over IP includes all necessary KVM cables, and offers KVM control from the BIOS-level onward. Reboot, monitor the entire boot process, and interact with your connected system easily. RS232 support also lets you connect to a serial console device via Telnet or SSH.

Virtual Media lets you execute files via USB from the remote console as if they were local to the connected server. Perfect for remote driver updates, patches, application or OS installation.

The Java-based browser utility ensures the IP remote control unit is compatible with many current web browsers, and almost any operating system on the market.

Multiple integrated security features ensure a reliable single port IP KVM connection, including password-protection, IP/MAC address filtering, external authentication (RADIUS, LDAP, LDAPS, Active Directory) and advanced encryption (56-bit DES, 168-bit 3DES, 256-bit AES, 128-bit RC4).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet





Användning

- Remote access to a mission-critical server
- BIOS level remote access to servers at co-location, ISP and MSP locations
- Small to Medium businesses that require access to individual servers without breaching security to others

Funktioner

- Full, BIOS-level control of a remote system over the internet
- Supports USB or PS/2 keyboard and mouse
- Supports resolutions up to 1600x1200
- Includes all necessary KVM Cables
- USB virtual media port for disk emulation and file transfers, including complete remote application and operating system installations
- Browser-based login for compatibility with most operating systems
- Java client available for Windows® systems
- Security features include: SSL Encrypted Login, IP/MAC filtering, Password Protection, Encryption (56-bit DES, 168-bit 3DES, 256-bit AES, 128-bit RC4) and External Authentication (RADIUS, LDAP, LDAPS, Active Directory)
- RS-232 console support for Telnet or SSH terminal access

Hårdvara

Garantipolicy	2 Years
Audio	Nej
KVM-portar	1
PC-gränssnitt	USB och PS/2
PC-videotyp	VGA

Flera skärmar	1
Hyllmonterbar	Ja
Medföljande kablar	Ja
Kedjekoppling	Nej

Prestanda

Skärmvisning (OSD) & stöd för snabbtangenter	Ja
DVI-stöd	Nej
IP-kontroll	Ja
Hot-Key Selection	Ja
Maximal analog upplösning	1600x1200 @ 60Hz
Stödda upplösningar	1600x1200, 1280x1024, 1280x720, 1152x864, 1024x768, 800x600, 720x400, 640x480
Stöd för portval	Genvägskommandon och OSD (visning på skärmen)
Säkerhetsfunktioner	128-bit SSL-kryptering AES DES 3DES RC4 IP-filtrering MAC-adressfiltrering
Stödda protokoll	TCP/IP, HTTP, HTTPS, UDP, DHCP, SSL, ARP, DNS, ICMP, CHAP, PPP RADIUS, LDAP, LDAPS, Active Directory

Kontakt(er)

Konsolgränssnitt		2 - PS/2 (6-stifts, Mini-DIN)
		2 - USB 2.0 Type-A (4 stift, 480 Mbps)
		1 - VGA (15-stifts, High Density D-Sub)
Värdkontakter		2 - PS/2 (6-stifts, Mini-DIN)
		1 - USB 2.0 Type-A (4 stift, 480 Mbps)
		1 - VGA (15-stifts, High Density D-Sub)
Övriga gränssnitt		1 - DB-9 (9-stifts, D-Sub)
		1 - RJ-45
		1 - USB Mini-B (5-stifts)

Mjukvara	OS-kompatibilitet	OS independent; No software or drivers required
----------	-------------------	---

Särskilda anmärkningar/krav	System- och kabelkrav	Connected server and remote user computers can be using any operating systems capable of running Sun Java Runtime Environment (JRE) 6, Update 3 or higher Browsers supported for remote login include: Internet Explorer, Chrome, Firefox, Safari, Opera, Mozilla and Netscape. Please refer to product manual for compatible version numbers
-----------------------------	-----------------------	--

Indikatorer	LED-indikatorer	1 - Power 1 - Link 1 - 10/100 Mbps (Orange/Green)
-------------	-----------------	---

Ström	Strömkälla	AC-adapter medföljer
	Inspänning	100 - 240 AC
	Inström	0.5 A
	Utspänning	5.3 DC

	Utström	2.4 A
	Polaritet på mittpol	Positiv
	Strömförbrukning	6.3 W
Miljö		
	Drifttemperatur	0°C to 50°C (32°F to 122°F)
	Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)
	Luftfuktighet	0~80% RH (Non-Condensing)
Utseende		
	Färg	Svart
	Kabinetttyp	Stål
	Produktlängd	7.9 in [20 cm]
	Produktbredd	3.1 in [8 cm]
	Produkthöjd	1.0 in [2.5 cm]
	Produktvikt	17.1 oz [485 g]
Förpackning		
	Förpackningsantal	1
	Paketets längd	10.4 in [26.5 cm]
	Paketets bredd	8.7 in [22 cm]
	Paketets höjd	3.7 in [95 mm]
	Fraktvikt (förpackning)	3.2 lb [1.4 kg]
Vad det är i lådan		
	Ingår i paketet	1 - IP KVM Switch
		1 - Console Cable
		1 - PS/2 KVM Cable
		1 - USB 2.0 Virtual Media Cable

- 1 - USB KVM Cable
- 1 - Rack Mount Kit
- 1 - Software CD
- 1 - Instruction Manual (on CD)
- 1 - Quick Start Guide

Warranty
Information

Warranty

2 År

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.