

16 Port 1U Rackmount USB PS/2 KVM Switch with OSD

Produkt ID: SV1631DUSBGB



The SV1631DUSBGB 16 Port 1U Rack Mount USB PS/2 KVM Switch with OSD offers a dependable computer management tool that allows you to control up to 16 USB or PS/2 connected computers from a single keyboard, mouse and monitor.

The KVM switch offers maximum control, allowing you to switch computers using hotkey commands or front panel push-buttons, and offers the added convenience of an On Screen Display to quickly access configuration options.

A suitable addition to server room operations, the 16 port switch can be rack-mounted into 1U of cabinet space, and can be cascaded with multiple KVM switches to deliver control of up to 136 computers from this single switch.

This high quality USB PS/2 KVM Switch is TAA compliant and backed by a StarTech.com 3-year warranty with free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Add single console administration to your Co-location/ISP facility saving you time and money
- Create a scalable, streamlined access solution in your Datacenter or Server Farm
- Perfect for manufacturing line computer control, simplifying access to multiple systems
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors,

keyboards and mice

Funktioner

- Connect USB and PS/2 based computer systems
- OS independent – No software or drivers required
- Auto-scan function cycles through computers sequentially
- Cascade configuration expands system capability
- Front panel push-buttons and Hot-key functions allow for easy switching
- On Screen Display (OSD) supports naming connected computers
- USB & PS2 console interfaces for keyboard and mouse
- OSD security option allows selected PCs to be password protected from unauthorized use
- Rugged, all-metal 1U chassis for use in harsh environments and space-saving cabinets

Hårdvara

Garantipolicy	3 Years
Audio	Nej
KVM-portar	16
PC-gränssnitt	USB och PS/2
PC-videotyp	VGA
Flera skärmar	1
Hyllmonterbar	Ja
Medföljande kablar	Nej
Kedjekoppling	Ja

Prestanda

Skärmvisning (OSD) & Nej
stöd för
snabbtangenter



IP-kontroll	Nej
Hot-Key Selection	Ja
Maximal analog upplösning	1920 x 1440 @60hz
Maximalt antal användare	1
Maximalt antal överlappade datorer	136
Stöd för portval	Tryckknapp och genvägskommandon
Medeltid mellan fel (MTBF)	158000 hours

Mjukvara

OS-kompatibilitet	OS independent; No software or drivers required
-------------------	---

Ström

Power Source	AC-adapter medföljer
Inspänning	100 - 240 AC
Inström	0.2 A
Utspänning	9V DC
Utström	0.6 A
Polaritet på mittpol	Positiv
Kontakttyp	M
Strömförbrukning	5.4

Miljö

Drifttemperatur	5°C to 40°C (41°F to 104°F)
Förvaringstemperatur	-20°C to 60°C (-4°F to 140°F)

Utseende

Kabinettyp	Stål
Produktlängd	17.2 in [43.8 cm]



Produktbredd	7.1 in [18 cm]
Produkt höjd	1.8 in [45 mm]
Produktvikt	6.9 lb [3.1 kg]

Förpackning

Package Length	23.4 in [59.5 cm]
Package Width	3.5 in [88 mm]
Package Height	10.4 in [26.4 cm]
Fraktvikt (förpackning)	8.4 lb [3.8 kg]

Vad det är i lådan

Ingår i paketet	16 Port KVM Switch
	Mounting Brackets
	PS/2 keyboard and mouse Y cable
	Power Adapter
	foot pads
	User Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

