

2 Port USB DisplayPort Cable KVM Switch w/ Audio and Remote Switch - USB Powered

Product ID: SV211DPUA



The SV211DPUA 2-Port DisplayPort Cable KVM Switch with Audio and Remote Switching Control lets you control two DisplayPort, USB equipped PCs with a single monitor, keyboard, mouse and audio peripheral set.

To help organize your desk without sacrificing work space, this compact DisplayPort USB KVM features integrated cables that can be connected directly to your system, while leaving a minimal footprint. The switch features a remote push-button on a 1.5 meter (5ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac compatible software for switching between systems. To eliminate the need for a bulky external power adapter and wall outlet, the DisplayPort KVM switch is USB-powered.

This KVM with DisplayPort video capability offers support for resolutions up to 2560x1600 for the ability to drive a large DisplayPort display for applications that require high graphical output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice
- Perfect for sharing computers and attached peripherals in the home or home office
- Dual system control for single user workstations increasing user productivity in the office

Features

- Switch PCs via push-button, hot-keys or switching software

- Space-saving design, minimal footprint
- Integrated KVM cables and remote switch
- Switching software supports PC and Mac platforms
- USB Powered - No external power adapter required
- Independent audio/mic switching for uninterrupted audio
- Supports hot-plugging
- Remote switch on 1.5m (5ft.) cable
- Supports resolutions up to 2560x1600
- Analog (3.5mm) and DisplayPort audio supported

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DisplayPort
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	No
IP Control	No
Hot-Key Selection	Yes
Audio Specifications	Analog (3.5mm) and DisplayPort audio supported
Port Selection Support	Push Button, Hotkeys, and Software



Connector(s)

Console Interface(s)	3.5 mm Mini-Jack (3 Position)
	USB Type-A (4 pin) USB 2.0
	DisplayPort (20 pin)
Host Connectors	USB Type-A (4 pin) USB 2.0
	3.5 mm Mini-Jack (3 Position)
	DisplayPort (20 pin)

Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10
	Windows Server 2003, 2008 R2, 2012, 2016, 2019
	Mac OS 10.6 to 10.9

Special Notes / Requirements

Note	OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform
	If you intend to convert the DisplayPort KVM to work with different video sources or displays such as HDMI or VGA, active adapters are required

Indicators

LED Indicators	PC Selection indicator
----------------	------------------------

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (4F to 140F)
Humidity	0~90% RH Non-Condensing

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	33.5 in [85 cm]



Product Length	3.5 in [88.0 mm]
Product Width	2.6 in [66.0 mm]
Product Height	0.9 in [23.0 mm]
Weight of Product	13.0 oz [367.0 g]

Packaging Information

Package Length	9.8 in [25.0 cm]
Package Width	6.4 in [16.3 cm]
Package Height	2.4 in [62.0 mm]
Shipping (Package) Weight	16.9 oz [480.0 g]

What's in the Box

Included in Package	KVM Switch
	Software CD
	Instruction Manual

**Product appearance and specifications are subject to change without notice.*

