

2 Port HDMI KVM Switch - 4K 60Hz - Compact Dual Port UHD/Ultra HD USB Desktop KVM Switch w/Integrated 4ft Cables & Audio - Bus Powered & Remote Switching - MacBook ThinkPad

Product ID: SV211HDUA4K



The SV211HDUA4K 2-Port 4K60Hz HDMI Cable KVM Switch with Audio and Remote Switching Control gives you control of two HDMI, USB equipped computers with a single monitor, keyboard, mouse and audio peripheral set.

The Dual HDMI KVM switch supports resolutions up to 4K at 60Hz and can drive one large HDMI display with ease, maximizing viewing space. With support for separate 3.5 mm stereo audio, the KVM switch delivers full audio compatibility across connected computers.

This HDMI KVM switch is OS independent, meaning it can work with virtually any laptop or desktop computer.

The switch features a remote push-button on a 1.5 meter (4ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and optional PC or Mac compatible software for switching between systems.

StarTech.com offers a wide selection of high-quality KVM switches and KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors.

The SV211HDUA4K is backed by a 2-year StarTech.com warranty and free lifetime multilingual technical support.

Certifications, Reports and Compatibility



Applications

Features

- Operate and access two HDMI computers from one workstation at 4K 60Hz resolutions
- Integrate into your set up quickly and easily with built-in 4 ft. KVM cables and a space-saving design
- Switch PCs via push-button, hot-keys or switching software
- Switching software supports Windows, Windows Server & macOS platforms
- USB Powered - No external power adapter required
- Independent audio/mic switching for uninterrupted audio Analog (3.5mm) and HDMI audio supported

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	HDMI
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	No
IP Control	No
Hot-Key Selection	Yes
Maximum Data Transfer Rate	480Mbps (USB 2.0)
Maximum Digital	3840 x 2160 (Ultra HD 4K) @ 60hz

Resolutions	
Wide Screen Supported	Yes
Audio Specifications	Two Channel Audio Input and Output
Auto Scan	10, 20, 30, 40, 50, and 60 seconds
Port Selection Support	Push Button, Hotkeys, and Software
MTBF	1,012,884 hours

Connector(s)

Console Interface(s)	2 - USB 2.0 Type-A (4 pin, 480Mbps) 1 - HDMI 2 - 3.5 mm Mini-Jack (3 Position)
Host Connectors	2 - USB 2.0 Type-A (4 pin, 480Mbps) 2 - HDMI 4 - 3.5 mm Mini-Jack (3 Position)

Software

OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10, 10 ARM, 11, 11 ARM Windows Server 2003, 2008 R2, 2012, 2016, 2019, 2022 Mac OS 10.6 to 10.12
------------------	--

Special Notes / Requirements

Note	In order to access the software and hotkeys of the KVMs, a compatible OS must be installed on the connected host, however the KVM and push button switching function is OS independent
------	--

Indicators

LED Indicators	2 - Orange
----------------	------------

Power

Power Source	Bus Powered
Input Voltage	5V DC
Output Voltage	5 DC

Environmental

Operating Temperature	0 ~ 40C
Storage Temperature	-20 ~ 60C
Humidity	0 ~ 90% RH, Non-Condensing

Physical Characteristics

Color	Black
Product Length	52.0 in [132.0 cm]
Product Width	3.8 in [9.7 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	15.2 oz [431 g]

Packaging Information

Package Quantity	1
Package Length	6.3 in [16 cm]
Package Width	9.8 in [25 cm]
Package Height	2.5 in [6.3 cm]
Shipping (Package) Weight	18.4 oz [522 g]

What's in the Box

Included in Package	1 - KVM Switch
	1 - Quick-Start Guide

**Product appearance and specifications are subject to change without notice.*