2 Port USB HDMI Cable KVM Switch with Audio and Remote Switch – USB Powered

Product ID: SV211HDUA

The SV211HDUA 2-Port HDMI Cable KVM Switch with Audio and Remote Switching Control lets you control two HDMI, USB equipped PCs with a single monitor, keyboard, mouse and audio peripheral set.

To help organize your desk without sacrificing work space, this compact HDMI USB KVM features integrated cables that can be connected directly to your system, while leaving a minimal footprint. The switch features a remote push-button on a 1.5 meter (5ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac compatible software for switching between systems. To eliminate the need for a bulky external power adapter and wall outlet, the HDMI KVM switch is USB-powered.

This KVM with HDMI video capability offers support for 1080p HD resolutions (up to 1920x1200) for the ability to drive a large HDMI display for applications that require high graphical output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

• Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice

• Perfect for sharing computers and attached peripherals in the home or home office

• Dual system control for single user workstations increasing user productivity in the office

Features

• Supports HD resolutions (1080p - 1920x1200)

• Switch PCs via push-button, hot-keys or switching software

• Space-saving design, minimal footprint

• Integrated KVM cables and remote switch

• Switching software supports PC and Mac platforms

General		
	UPC	065030851060
	Package Quantity	1
	Warranty	2 Years
Special Notes / Requirements		
	Special Notes	OS Compatibility refers to KVM software only - the KVM itself can be used without software on any platform
Power		
	Power Source	USB-Powered
Physical & Environmental		
	Color	Black
	Material	Plastic
	Cable Length	33.5 in [85 cm]
	Product Length	3.5 in [88.0 mm]
	Product Width	2.6 in [66.0 mm]
	Product Height	0.9 in [23.0 mm]
	Weight of Product	12.4 oz [350.0 g]

	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (4F to 140F)
	Humidity	0~90% RH Non-Condensing
Performance		
	IP Control	No
	Hot-Key Selection	Yes
	Port Selection Support	Push Button, Hotkeys, and Software
	On-Screen Display	No
Hardware		
	CAC Support	No
	Audio	Yes
	Number of KVM Ports	2
	Supported Platforms	USB
	PC Video Type	HDMI
	Number of Monitors Supported	1
	Rack-Mountable	No
	Cables Included	Yes
	Industry Standards	HDCP
	Cascadable	No
	LED Indicators	1 - PC Selection indictor
Packaging & In-the-Box		
	Included in Package	1 - KVM Switch
		1 - Software CD
		1 - Instruction Manual
	Package Width	9.9 in [25.1 cm]

	Package Depth	6.4 in [16.2 cm]
	Package Height	2.6 in [65 mm]
	Shipping (Package) Weight	16.0 oz [452 g]

Connector(s)		
	Host Connector 1 (Quantity)	1
	Host Connector 1	USB-A (480Mbps, 2.5W)
	Host Connector 2 (Quantity)	1
	Host Connector 2	HDMI
	Host Connector 3 (Quantity)	2
	Host Connector 3	3.5mm (3 Conductors, TRS)
	Connector 1 (Quantity)	1
	Connector 1	HDMI
	Connector 2 (Quantity)	2
	Connector 2	3.5mm (3 Conductors, TRS)
	Connector 3 (Quantity)	2
	Connector 3	USB-A (480Mbps, 2.5W)

***Product appearance and specifications are subject to change without notice.**