2 Port USB DVI KVM Switch Kit with Cables USB 2.0 Hub & Audio

Product ID: SV211KDVI

The SV211KDVI 2 Port USB DVI KVM Switch Kit with Cables USB 2.0 Hub & Audio provides control of two DVI enabled, USB controlled computers, as well as independent audio/microphone switching for uninterrupted audio when switching between PCs.

This USB+DVI KVM Switch features support for high-resolution digital (1920x1200) and analog (2048x1536) video, plus an integrated USB 2.0 hub that allows you to share 2 high-speed USB devices between computers.

Compatible with Mac, Linux and Windows based computers, this compact DVI KVM is a great space-saving solution for a broad range of environments including SOHO (Small or Home Offices), gaming, multimedia production and more.

A complete, out-of-the-box solution, this DVI KVM Switch includes two 4 ft. DVI/Audio & Mic combo cables that simplify computer connection to the switch and help to eliminate cable clutter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

• Ideal for conserving space when working with multiple desktops, workstations and servers

• Home/SOHO/multimedia environment dual system control for single user workstations

• Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required

• Applicable for call centers, help desks, education environments, home gamers, and PC enthusiasts

Features

• Supports resolutions up to 1920x1200(digital) and 2048x1536(analog)

• Integrated USB 2.0 hub allows you to share up to two high-speed USB devices between computers

• Compatible with all USB supported Operating Systems

• Compact design saves space

• Computer selection by push button, keyboard hotkeys and Switching Software (for Windows/Mac)

• Hot Pluggable - add or remove computers without having to power down

• LED indicators for easy status monitoring

• USB 2.0/1.1 specification compliant

• HDCP Compliant

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DVI
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	No
DVI Support	Yes
IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	2048x1536
Maximum Digital Resolutions	1920x1200
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

Connector(s)

Console Interface(s)	2 - 3.5 mm Mini-Jack (3 Position)
	1 - DVI-I (29 pin)
	2 - USB 2.0 Type-A (4 pin, 480Mbps)
Host Connectors	2 - DVI-I (29 pin)
	2 - USB B (4 pin)
Other Interface(s)	2 - USB 2.0 Type-A (4 pin, 480Mbps)

Software

OS Compatibility	OS independent; No software or drivers required

Indicators

LED Indicators	1 - Power/Computer Selection Indicator

Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A

	Center Tip Polarity	Positive
	Plug Type	N
	Power Consumption (In Watts)	10
Environmental		
	Operating Temperature	0C to 40C (32F to 104F)
	Storage Temperature	-20C to 60C (-4F to 140F)
	Humidity	0~90% RH
Physical Characteristics		
	Color	White
	Material	Plastic
	Product Length	6.1 in [15.4 cm]
	Product Width	2.6 in [6.6 cm]
	Product Height	1.1 in [2.7 cm]
	Weight of Product	6.0 oz [170.0 g]
Packaging Information		
	Package Quantity	1
	Package Length	8.2 in [20.8 cm]
	Package Width	5.6 in [14.2 cm]
	Package Height	7.2 in [18.2 cm]
	Shipping (Package) Weight	2.7 lb [1.2 kg]
What's in the Box		
	Included in Package	1 - 2 Port DVI USB KVM
		2 - 4 ft. DVI/Audio&Mic combo cables
		2 - 4 ft. USB cables

1 - Power Adapter

Product appearance and specifications are subject to change without notice.