

## 2 Port USB DVI KVM Switch Kit with Cables USB 2.0 Hub & Audio

**Product ID:** SV211KDVI



The SV211KDVI 2 Port USB DVI KVM Switch Kit with Cables USB 2.0 Hub & Audio provides control of two DVI enabled, USB controlled computers, as well as independent audio/microphone switching for uninterrupted audio when switching between PCs.

This USB+DVI KVM Switch features support for high-resolution digital (1920x1200) and analog (2048x1536) video, plus an integrated USB 2.0 hub that allows you to share 2 high-speed USB devices between computers.

Compatible with Mac, Linux and Windows based computers, this compact DVI KVM is a great space-saving solution for a broad range of environments including SOHO (Small or Home Offices), gaming, multimedia production and more.

A complete, out-of-the-box solution, this DVI KVM Switch includes two 4 ft. DVI/Audio & Mic combo cables that simplify computer connection to the switch and help to eliminate cable clutter.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Ideal for conserving space when working with multiple desktops, workstations and servers
- Home/SOHO/multimedia environment dual system control for single user workstations
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required
- Applicable for call centers, help desks, education environments, home gamers, and PC enthusiasts

## Features

- Supports resolutions up to 1920x1200(digital) and 2048x1536(analog)
- Integrated USB 2.0 hub allows you to share up to two high-speed USB devices between computers
- Compatible with all USB supported Operating Systems
- Compact design saves space
- Computer selection by push button, keyboard hotkeys and Switching Software (for Windows/Mac)
- Hot Pluggable - add or remove computers without having to power down
- LED indicators for easy status monitoring
- USB 2.0/1.1 specification compliant
- HDCP Compliant

---

### Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DVI
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

---

### Performance

On-Screen Display	No
DVI Support	Yes
IP Control	No
Hot-Key Selection	Yes



Maximum Analog Resolutions	2048x1536
Maximum Digital Resolutions	1920x1200
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

---

#### Connector(s)

Console Interface(s)	DVI-I (29 pin)
	3.5 mm Mini-Jack (3 Position)
	USB Type-A (4 pin) USB 2.0
Host Connectors	DVI-I (29 pin)
	USB B (4 pin)
Other Interface(s)	USB Type-A (4 pin) USB 2.0

---

#### Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

#### Indicators

LED Indicators	Power/Computer Selection Indicator
----------------	------------------------------------

---

#### Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	10

---



### Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~90% RH

---

### Physical Characteristics

Color	White
Material	Plastic
Product Length	6.1 in [15.4 cm]
Product Width	2.6 in [65.5 mm]
Product Height	1.1 in [27.0 mm]
Weight of Product	6.0 oz [170.0 g]

---

### Packaging Information

Package Length	8.2 in [20.8 cm]
Package Width	5.6 in [14.2 cm]
Package Height	7.2 in [18.2 cm]
Shipping (Package) Weight	2.7 lb [1.2 kg]

---

### What's in the Box

Included in Package	2 Port DVI USB KVM
	Power Adapter
	4 ft. DVI/Audio&Mic combo cables
	4 ft. USB cables

---

***\*Product appearance and specifications are subject to change without notice.***

