

2 Port USB DVI KVM Switch with Audio and Cables

ID del Producto: SV211KDVIGB



This USB DVI KVM Switch provides access and control of two DVI enabled, USB controlled computers, as well as independent audio/microphone switching that allows an uninterrupted audio experience, even when switching back and forth between computers.

The perfect KVM switch for multimedia applications, SV211KDVIGB supports both digital and analog video signal transmissions for display resolutions of up to 1900x1200 (digital) and 2048x1536 (analog). The switch also features an integrated USB 2.0 hub that allows you to share two high-speed USB devices between computers.

Compatible with Mac, Linux or PC Based computers, the DVI KVM switch (SV211KDVIGB) is a great addition for a broad range of environments including SOHO (Small or Home Offices), gaming, multimedia production workstations and more, and features a compact form factor design that helps preserve valuable desk space.

A complete, out-of-the-box solution, this DVI KVM Switch (SV211KDVIGB) includes two 4 ft. DVI/Audio & Mic combo cables that simplify computer connection to the switch and help to eliminate the cable clutter that could result from using multiple cables.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Ideal for desktops, workstations and servers with Flat Panel LCD monitors.
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required.
- Sharing computers and USB devices in the home/SOHO/multimedia environment/

Características

- Compact design saves space
- Compatible with all USB supported Operating Systems.
- Computer selection by push button, keyboard hotkeys and Switching Software(for Windows/Mac)
- Designed for high-resolution applications: 1920 x 1200 digital resolution and 2048 x 1536 analog resolution
- Hot Pluggable - add or remove computers without having to power down the switch
- Integrated USB 2.0 hub allows you to share up to two high-speed USB devices between computers
- LED indicators for easy status monitoring.
- USB 2.0/1.1 specification compliant.
- HDCP Compliant

Hardware

Política de Garantía	2 Years
Soporte de Audio	Sí
Cantidad de Puertos KVM	2
Plataformas Admitidas	USB
Tipo de Video PC	DVI
Soporte de Pantalla Doble	1
Montaje en Rack	No

Cables Incluidos	Sí
Sistema En Cascada	No

Rendimiento

Soporta OSD y Teclas de Acceso Directo	No
Soporte DVI	Sí
Control IP KVM	No
Hot-Key Selection	Sí
Resolución Analógica Máxima	2048x1536
Resolución Digital Máxima	1920x1200
Cantidad Máxima de Usuarios	1
Soporte para Selección de Puertos	Botón Pulsador y Teclas de Acceso Directo

Conector(es)

Interfaz(ces) de Consola	2 - Enchufe mini-jack de 3,5mm (3 posiciones)
	1 - DVI-I (29 pines)
	2 - USB 2.0 Tipo A (4 pines, 480Mbps)
Conectores del Host	2 - DVI-I (29 pines)
	2 - USB B (4 pines)

Software

Compatibilidad OS	OS independent; No software or drivers required
-------------------	---

Requisitos de Energía

Fuente de alimentación	Adaptador de alimentación de CA incluido
Tensión de Entrada	100 - 240 AC

Corriente de Entrada	0.4A
Tensión de Salida	5 DC
Alimentación de Salida	2A
Polaridad Central	Positivo
Tipo de Enchufe	N
Consumo de Energía	10

Características Físicas

Color	Blanco
Tipo de Gabinete	Plástico
Longitud del Producto	0.0 in [0.0 mm]
Ancho del Producto	6.1 in [15.4 cm]
Altura del Producto	1.1 in [2.7 cm]
Profundidad del Producto	2.6 in [65.5 mm]
Peso del Producto	5.6 oz [160.0 g]

Información de la Caja

Cantidad de Paquetes	1
Longitud de la Caja	8.2 in [20.8 cm]
Ancho de la Caja	5.6 in [14.2 cm]
Altura de la Caja	7.1 in [18.0 cm]
Peso (de la Caja) del Envío	2.8 lb [1.2 kg]

Contenido de la Caja

Incluido en la Caja	1 - 2 Port KVM
---------------------	----------------

2 - 4 ft. DVI/Audio&Mic combo cables

2 - 4 ft. USB cables

1 - Power Adapter

1 - Software CD

Información Acerca
de la Garantía

Warranty

2 Años

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.