

2 Port USB DVI KVM Switch with Audio and Cables

Productcode: SV211KDVIGB



This USB DVI KVM Switch provides access and control of two DVI enabled, USB controlled computers, as well as independent audio/microphone switching that allows an uninterrupted audio experience, even when switching back and forth between computers.

The perfect KVM switch for multimedia applications, SV211KDVIGB supports both digital and analog video signal transmissions for display resolutions of up to 1900x1200 (digital) and 2048x1536 (analog). The switch also features an integrated USB 2.0 hub that allows you to share two high-speed USB devices between computers.

Compatible with Mac, Linux or PC Based computers, the DVI KVM switch (SV211KDVIGB) is a great addition for a broad range of environments including SOHO (Small or Home Offices), gaming, multimedia production workstations and more, and features a compact form factor design that helps preserve valuable desk space.

A complete, out-of-the-box solution, this DVI KVM Switch (SV211KDVIGB) includes two 4 ft. DVI/Audio & Mic combo cables that simplify computer connection to the switch and help to eliminate the cable clutter that could result from using multiple cables.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Ideal for desktops, workstations and servers with Flat Panel LCD monitors.
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required.
- Sharing computers and USB devices in the home/SOHO/multimedia environment/

Eigenschappen

- Compact design saves space
- Compatible with all USB supported Operating Systems.
- Computer selection by push button, keyboard hotkeys and Switching Software(for Windows/Mac)
- Designed for high-resolution applications: 1920 x 1200 digital resolution and 2048 x 1536 analog resolution
- Hot Pluggable - add or remove computers without having to power down the switch
- Integrated USB 2.0 hub allows you to share up to two high-speed USB devices between computers
- LED indicators for easy status monitoring.
- USB 2.0/1.1 specification compliant.
- HDCP Compliant

Hardware

Garantiebeleid	2 Years
Audio	Ja
KVM-poorten	2
Ondersteunde platforms	USB
PC-videotype	DVI
Multi-monitor	1
Rack-monteerbaar	Nee

Inclusief kabels	Ja
Op elkaar aansluitbaar	Nee

Prestaties

Schermmenu & sneltoetsen	Nee
DVI-ondersteuning	Ja
IP-controle	Nee
Hot-Key Selection	Ja
Maximale analoge resoluties	2048x1536
Maximale digitale resoluties	1920x1200
Maximum aantal gebruikers	1
Poortselectie-ondersteuning	Knopdruk en sneltoetsen

Connector(en)

Console-aansluiting(en)	2 - 3,5 mm mini-jack (3 standen)
	1 - DVI-I (29-polig)
	2 - USB 2.0 Type-A (4 pin, 480Mbps)
Hostaansluitingen	2 - DVI-I (29-polig)
	2 - USB B (4-polig)

Software

Besturingssystemen	OS independent; No software or drivers required
--------------------	---

Voeding

Voedingsbron	Inclusief wisselstroomadapter
Ingangsspanning	100 - 240 AC
Ingangsstroom	0.4A

Uitgangsspanning	5 DC
Uitgangsstroom	2A
Polariteit pin midden	Positief
Stekkertype	N
Vermogensopname	10

Fysieke eigenschappen

Kleur	Wit
Type behuizing	Kunststof
Lengte product	0.0 in [0.0 mm]
Breedte product	6.1 in [15.4 cm]
Hoogte product	1.1 in [2.7 cm]
Diepte product	2.6 in [65.5 mm]
Gewicht product	5.6 oz [160.0 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	8.2 in [20.8 cm]
Package Width	5.6 in [14.2 cm]
Package Height	7.1 in [18.0 cm]
Verzendgewicht (verpakt)	2.8 lb [1.2 kg]

Wat wordt er meegeleverd

Meegeleverd	1 - 2 Port KVM
	2 - 4 ft. DVI/Audio&Mic combo cables
	2 - 4 ft. USB cables

1 - Power Adapter

1 - Software CD

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.