

## 2 Port USB DVI KVM Switch with Audio and Cables

**Product ID:** SV211KDVIGB



This USB DVI KVM Switch provides access and control of two DVI enabled, USB controlled computers, as well as independent audio/microphone switching that allows an uninterrupted audio experience, even when switching back and forth between computers.

The perfect KVM switch for multimedia applications, SV211KDVIGB supports both digital and analog video signal transmissions for display resolutions of up to 1900x1200 (digital) and 2048x1536 (analog). The switch also features an integrated USB 2.0 hub that allows you to share two high-speed USB devices between computers.

Compatible with Mac, Linux or PC Based computers, the DVI KVM switch (SV211KDVIGB) is a great addition for a broad range of environments including SOHO (Small or Home Offices), gaming, multimedia production workstations and more, and features a compact form factor design that helps preserve valuable desk space.

A complete, out-of-the-box solution, this DVI KVM Switch (SV211KDVIGB) includes two 4 ft. DVI/Audio & Mic combo cables that simplify computer connection to the switch and help to eliminate the cable clutter that could result from using multiple cables.

## Certifications, Reports and Compatibility

### Applications

- Ideal for desktops, workstations and servers with Flat Panel LCD monitors.
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required.
- Sharing computers and USB devices in the home/SOHO/multimedia environment/

## Features

- Compact design saves space
- Compatible with all USB supported Operating Systems.
- Computer selection by push button, keyboard hotkeys and Switching Software(for Windows/Mac)
- Designed for high-resolution applications: 1920 x 1200 digital resolution and 2048 x 1536 analog resolution
- Hot Pluggable - add or remove computers without having to power down the switch
- Integrated USB 2.0 hub allows you to share up to two high-speed USB devices between computers
- LED indicators for easy status monitoring.
- USB 2.0/1.1 specification compliant.
- HDCP Compliant

---

### Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DVI
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

---

### Performance

On-Screen Display	No
DVI Support	Yes
IP Control	No
Hot-Key Selection	Yes
Maximum Analog	2048x1536



Resolutions	
Maximum Digital Resolutions	1920x1200
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

---

**Connector(s)**

Console Interface(s)	3.5 mm Mini-Jack (3 Position) DVI-I (29 pin) USB Type-A (4 pin) USB 2.0
Host Connectors	DVI-I (29 pin) USB B (4 pin)

---

**Software**

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.4A
Output Voltage	5 DC
Output Current	2A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	10

---

**Physical Characteristics**

Color	White
Material	Plastic
Product Length	0.0 in [0.0 mm]



Product Width	6.1 in [15.4 cm]
Product Height	1.1 in [27.0 mm]
Product Depth	2.6 in [65.5 mm]
Weight of Product	5.6 oz [160.0 g]

---

**Packaging Information**

Package Length	8.2 in [20.8 cm]
Package Width	5.6 in [14.2 cm]
Package Height	7.1 in [18.0 cm]
Shipping (Package) Weight	2.8 lb [1.2 kg]

---

**What's in the Box**

Included in Package	2 Port KVM
	4 ft. DVI/Audio&Mic combo cables
	4 ft. USB cables
	Power Adapter
	Software CD

---

***\*Product appearance and specifications are subject to change without notice.***

