

2 Port Black USB KVM Switch Kit with Audio and Cables

Product ID: SV211KUSB



The SV211KUSB 2 Port USB KVM Switch Kit with Audio and Cables lets you control two USB-enabled computers using a single keyboard, mouse and VGA monitor and offers both hotkey and top panel push-button operation for simple switching between connected computers.

Designed to integrate seamlessly into any environment, the USB KVM switch offers a small footprint design (roughly the size of a deck of playing cards) and draws power from the connected computers, so it doesn't require an external power supply.

A suitable solution for virtually any application, the USB KVM switch supports video resolutions of up to 2048 x 1536 as well as audio switching. The USB KVM switch includes two 4ft 2-in-1 VGA and USB Host Cables, providing everything needed for quick installation to provide a complete, out-of-the-box KVM solution.

Delivering dependable and convenient control of multiple computers from a single peripheral station, the KVM switch is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Control 2 USB-enabled computers using a single keyboard, mouse, and VGA monitor
- Applicable for call centers, help desks, education environments, home gamers, video editing, and PC enthusiasts
- Great for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice
- Dual system control for single user workstations, increasing user productivity in the office

Features

- Cables (4 ft.) included
- Includes audio support for a complete switching solution
- Maximum resolution: 2048 x 1536
- Switching type: Hotkey, push-button
- Small footprint design
- USB Powered - No external adapter required

Hardware	Warranty	2 Years
	Audio	Yes
	KVM Ports	2
	PC Interface	USB
	PC Video Type	VGA
	Number of Monitors Supported	1
	Rack-Mountable	No
	Cables Included	Yes
	Daisy-Chain	No
Performance	On-Screen Display	No
	IP Control	No
	Hot-Key Selection	Yes
	Maximum Analog Resolutions	2048x1536 @60Hz
	Maximum Number of Users	1 Push Button and Hotkeys
	Port Selection Support	
Connector(s)	Console Interface(s)	USB Type-A (4 pin) USB 2.0
	Console Interface(s)	VGA (15 pin, High Density D-Sub)
	Console Interface(s)	3.5 mm Mini-Jack (3 Position)
	Host Connectors	VGA (15 pin, High Density D-Sub)
	Host Connectors	USB Mini-B (5 pin)
Software	OS Compatibility	OS independent; No software or drivers required
Power	Power Source	USB-Powered

Physical Characteristics	Color	Black
	Material	Plastic
	Cable Length	4.0 ft [1.2 m]
	Product Length	3.8 in [97.000 mm]
	Product Width	3.8 in [96 mm]
	Product Height	0.8 in [20 mm]
	Product Depth	2.4 in [60 mm]
	Weight of Product	3.3 oz [94 g]
<hr/>		
Packaging Information	Package Length	8.5 in [2.2 cm]
	Package Width	3.5 in [89 mm]
	Package Height	3.4 in [87 mm]
	Shipping (Package) Weight	22.7 oz [642 g]
<hr/>		
What's in the Box	Included in Package	2 Port KVM Switch
	Included in Package	4ft. VGA USB KVM Cable
	Included in Package	4ft. Audio Cable (3.5mm speaker/mic)
	Included in Package	Instruction Manual
	Included in Package	Driver CD

****Product appearance and specifications are subject to change without notice.***

