

## 2 Port USB DVI Cable KVM Switch with Audio

**Product ID:** SV215MICDVIA



The SV215MICDVIA 2 Port USB DVI Cable KVM Switch with Audio allows you to control 2 computers from a single KVM (Keyboard, Video, Mouse) peripheral set, and supports resolutions up to 1920x1200.

This cable-style KVM switch includes all of the cables and connections required, for a complete KVM solution. Plus, the switch features independent audio/mic switching to ensure uninterrupted sound, even when switching between computers.

This broadly compatible USB KVM switch can be connected to Mac, Linux or PC-based computers, making it a convenient solution for most operating environments. Plus, because of its space-saving "KVM-on-a-cable" design, no desk space is required for installation - an ideal choice for most applications, including SOHO (small or home offices), gaming, multimedia production workstations and more.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Control multiple desktops, workstations or servers that require full multi-media support
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required
- Sharing computers and attached peripherals in the home/SOHO/multimedia environment
- Great for PC test/burn-in computer control saving the desk space required for multiple monitors, keyboards and mice and allows remote access

## Features

- Micro cable KVM design with all necessary cables included
- Operating System independent - No software or driver required
- Includes Remote Selector switch and supports hot-key computer selection
- Supports resolutions up to 1920x1200
- Hot Plug - add or remove computers without reboot
- LED indicators for easy status monitoring
- USB 2.0/1.1 specification compliant
- HDCP Compliant

---

### Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DVI
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

---

### Performance

On-Screen Display	No
DVI Support	Yes - Single Link
IP Control	No
Hot-Key Selection	Yes
Maximum Digital Resolutions	1920 x 1200



Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

---

#### Connector(s)

Console Interface(s)	DVI-D (19 pin) USB Type-A (4 pin) USB 2.0 3.5 mm Mini-Jack (3 Position)
Host Connectors	DVI-D (19 pin) USB Type-A (4 pin) USB 2.0 3.5 mm Mini-Jack (3 Position)

---

#### Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

#### Special Notes / Requirements

Note	One host cable is 47 inches long, the other is 24 inches. Remote selector is 70 inches long
------	---

---

#### Environmental

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~80%RH

---

#### Physical Characteristics

Color	Black
Material	Plastic
Weight of Product	21.9 oz [620 g]

---

#### Packaging Information

Package Length	9.8 in [24.8 cm]
Package Width	3.4 in [86 mm]



Package Height	6.1 in [15.5 cm]
Shipping (Package) Weight	25.4 oz [720 g]

---

**What's in the Box**

Included in Package	2 Port Integrated KVM
	Remote Selector
	Manual

---

***\*Product appearance and specifications are subject to change without notice.***

