

2 Port USB VGA Cable KVM Switch with Audio

Product ID: SV215MICUSBA



The SV215MICUSBA 2 Port USB VGA Cable KVM Switch with Audio offers a high resolution (up to 2048x1536) solution for accessing and controlling two desktop computers from a single KVM (Keyboard, Video, Mouse) peripheral set.

A complete solution, this cable-style KVM switch includes all of the cables and connections required to share one monitor, keyboard and mouse, as well as speakers, across two computers. Plus, the switch features independent audio/microphone switching to ensure an uninterrupted audio experience, even when switching between computers.

Compatible with Mac, Linux or PC based computers the SV215MICUSBA is the perfect addition for a broad range of environments, and because of its space-saving “KVM-on-a-cable” design, no desk space is required for installation - an ideal choice for most environments, including SOHO (small or home offices), gaming, multimedia production workstations and more.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for desktops, workstations and servers that require full multi-media support
- Ideal for graphic designers, engineers, multi-media designers, and industries using CAD/CAM applications, where high resolution display units are required
- Sharing computers and attached peripherals in the home/SOHO/multimedia environment

Features

- Complete micro design saves space and money
- Compatible with all USB supported Operating Systems
- Designed for high-resolution applications: 2048x1536 analog resolution with DDC2B
- Computer selection by Remote selector and keyboard hotkeys
- Hot Pluggable - add or remove computers without having to power down the computers
- LED indicators for easy status monitoring
- USB 2.0/1.1 specification compliant

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	No
DVI Support	No
IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	2048x1536
Maximum Number of Users	1



Port Selection Support Push Button and Hotkeys

Connector(s)

Console Interface(s)	VGA (15 pin, High Density D-Sub) USB Type-A (4 pin) USB 2.0 3.5 mm Mini-Jack (3 Position)
Host Connectors	VGA (15 pin, High Density D-Sub) USB Type-A (4 pin) USB 2.0 3.5 mm Mini-Jack (3 Position)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Special Notes / Requirements

Note	One host cable is 47 inches long, the other is 24 inches. Remote selector cable is 70 inches long
------	---

Physical Characteristics

Color	Black
Material	Plastic
Product Length	31.9 in [81 cm]
Product Width	27.2 in [69 cm]
Product Height	10.2 in [26 cm]
Weight of Product	14.1 oz [400 g]

Packaging Information

Package Length	9.8 in [24.8 cm]
Package Width	3.4 in [86 mm]
Package Height	6.1 in [15.5 cm]
Shipping (Package) Weight	19.8 oz [560 g]



**What's in the
Box**

Included in Package	2 Port Integrated KVM
	Remote Selector
	Manual

****Product appearance and specifications are subject to change without notice.***

