

2 Port VGA Dual Monitor KVM Switch with PS/2

Product ID: SV221DD



This compact 2-port dual monitor KVM switch (VGA+VGA) offers the ultimate in convenience and cost-savings.

The dual VGA KVM switch lets you instantly switch back and forth between PCs at the touch of a button, while maintaining professional-quality video (up to 1920x1440) on both monitors.

An ideal solution for graphic designers, CAD/CAM designers or any project requiring dual monitor KVM control, the switch features a compact design, with cable entry positioned at the rear of the switch, saving valuable desk space and eliminating clutter.

A suitable multi-computer control solution for any workspace, the dual view KVM switch features a durable metal casing and is backed by our 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Control up to 2 computers with 1 keyboard, Mouse and 2 monitors
- Used in computers with Dual-VGA Cards
- Ideal for financial/banking industries, graphic designers, multi-media applications and industries using CAD/CAM applications

Features

- Offers direct channel selection using front panel push button and keyboard hotkeys

- Supports a high VGA resolution of up to 1920 x 1440 pixels
- All cables are connected to the rear for a more secure and neat connection
- Supports hot-plugging of PS/2 keyboards and mice including M/S IntelliMouse, Explorer, Optical mice and Logitech Netmouse
- Operating system independent, compatible with all operating systems
- Buzzer sound for port switching confirmation
- Power-free operation draws power from attached computers and requires no power adapters
- Numerical LED indicator for easy port status monitoring

Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	PS/2
PC Video Type	VGA
Number of Monitors Supported	Yes
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

Performance

DVI Support	No
IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	1920x1440
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys



Connector(s)

Console Interface(s)	PS/2 (6 pin, Mini-DIN)
	VGA (15 pin, High Density D-Sub)
Host Connectors	PS/2 (6 pin, Mini-DIN)
	VGA (15 pin, High Density D-Sub)

Power

Power Source	Not Included (not required for standard applications)
Output Voltage	9V DC
Output Current	0.6A
Center Tip Polarity	Negative
Plug Type	N

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)

Physical Characteristics

Color	Black
Material	Steel
Product Width	5.5 in [14 cm]
Product Height	2.4 in [60 mm]
Product Depth	3.4 in [86 mm]
Weight of Product	35.3 oz [1000 g]

Packaging Information

Package Length	10.6 in [27 cm]
Package Width	3.1 in [80 mm]
Package Height	7.2 in [18.4 cm]
Shipping (Package) Weight	29.7 oz [840 g]



What's in the Box

Included in Package	2 Port KVM Switch
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

