

2 Port DVI Dual Monitor KVM Switch with PS/2

Product ID: SV221DVIDD



This compact 2-port dual monitor KVM switch (DVI+DVI) offers the ultimate in convenience and cost-savings.

The dual DVI KVM switch lets you instantly switch back and forth between PCs at the touch of a button, while maintaining professional-quality video on both monitors (high digital resolution of up to 1280 x 1024, analog resolutions up to 1920 x 1440).

An ideal solution for graphic designers, CAD/CAM designers or any project requiring dual view KVM control, the switch features a compact design, with cable entry positioned at the rear of the switch, saving valuable desk space and eliminating clutter.

A suitable multi-computer control solution for any workspace, the dual DVI KVM switch features a durable metal casing and is backed by our 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Designed for Dual DVI monitor enabled PCs
- Ideal for environments using desktops, workstations and servers with Flat Panel LCD monitors

Features

- DVI-I interface technology supports both digital and analog video signal transmission
- Switches instantly between two PCs

- Rear connections provide a neat and secure environment
- Supports PS/2 keyboards and mouse including M/S IntelliMouse, Explorer and Logitech NetMouse
- Keyboard and mouse are hot pluggable, eliminating the need to reboot your systems
- Operating system independent
- Front panel LED's indicate which computer is active
- Supports high digital resolution of up to 1280 x 1024 and analog resolution of up to 1920 x 1440
- Draws power from your computer's PS/2 port, does not require a power adapter
- HDCP Compliant

Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	PS/2
PC Video Type	DVI
Number of Monitors Supported	Yes
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

Performance

DVI Support	Yes
IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	1920x1440 (not intended for use with Widescreen displays)
Maximum Digital Resolutions	1280x1024
Maximum Number of	1



Users	
Port Selection Support	Push Button and Hotkeys

Connector(s)

Console Interface(s)	DVI-I (29 pin) PS/2 (6 pin, Mini-DIN)
Host Connectors	DVI-I (29 pin) PS/2 (6 pin, Mini-DIN)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Indicators

LED Indicators	Port Status (Numerical display)
----------------	---------------------------------

Power

Power Source	Not Included (not required for standard applications)
Output Voltage	9V DC
Output Current	0.5A
Power Consumption (In Watts)	0.5W

Environmental

Operating Temperature	0C to 40C (32F to 104F)
-----------------------	-------------------------

Physical Characteristics

Color	Black
Material	Steel
Product Width	5.5 in [14 cm]
Product Height	2.4 in [62 mm]
Product Depth	3.4 in [86 mm]
Weight of Product	18.4 oz [520 g]

Packaging



Information

Package Length	9.2 in [23.3 cm]
Package Width	1.6 in [40 mm]
Package Height	5.7 in [14.6 cm]
Shipping (Package) Weight	30.7 oz [870 g]

What's in the Box

Included in Package	2 Port KVM Switch
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

