

## 2 Port Micro PS/2 VGA Cable KVM Switch

**Product ID:** SV221MICRO



This 2-port Micro KVM switch lets you take command of two PS/2-controlled computers from a single console, without sacrificing any desk space.

A space-saving and cost-effective computer management solution, the compact Micro KVM switch can be hung or tied up out of the way to free up work space, and features ultra-thin cables built on to the switch, leaving zero footprint once installed.

The Micro KVM switch draws power from connected computers and doesn't require an external power source - eliminating the need to position the switch near an available power outlet and saving the space required for a power cable.

Don't let the size fool you! This high quality Micro KVM switch delivers robust display capability with support for resolutions up to 2048x1536 (@60Hz) and supports hot plug-and-play installation for easy deployment.

Designed to ensure a seamlessly dependable operating experience, the 2-port Micro KVM switch is backed by StarTech.com's 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Allows control of 2 computers from 1 user console
- Perfect for integrating two different enterprise computer systems

### Features

- Automatically switch between 2 computer using the hot key commands
- Dependable 3-year Warranty
- Designed to integrate into your existing IT infrastructure and requires no software to be installed
- Plug n Play support allows users to change computers without any interruptions
- Supports MS Intellimouse (Pro Version), Explorer and Optical Mouse
- Ultra compact design and thin coaxial cables increases the availability and manageability of the server or workstation environment by using only one keyboard, monitor and a mouse

---

**Hardware**

Warranty	3 Years
Audio	No
KVM Ports	2
PC Interface	PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

---

**Performance**

DVI Support	No
IP Control	No
Hot-Key Selection	No
Maximum Analog Resolutions	2048x1536
Maximum Number of Users	1

---

**Connector(s)**

Console Interface(s)	PS/2 (6 pin, Mini-DIN)
----------------------	------------------------



	VGA (15 pin, High Density D-Sub)
Host Connectors	PS/2 (6 pin, Mini-DIN)
	VGA (15 pin, High Density D-Sub)

---

**Indicators**

LED Indicators	CPU A/B Selection indicators
----------------	------------------------------

---

**Physical Characteristics**

Material	Plastic
Cable Length	6.0 ft [1.8 m]
Product Length	3.0 in [75.6 mm]
Product Width	0.5 in [11.8 mm]
Product Height	1.1 in [27.6 mm]
Weight of Product	13.4 oz [380 g]

---

**Packaging Information**

Package Length	7.2 in [18.3 cm]
Package Width	2.0 in [50 mm]
Package Height	11.7 in [29.8 cm]
Shipping (Package) Weight	16.6 oz [470.0 g]

---

**What's in the Box**

Included in Package	2 Port Micro KVM on Cable
	Hot Key Reference Strip
	Instructional Manual

---

***\*Product appearance and specifications are subject to change without notice.***

