

2 Port USB VGA Cable KVM Switch - USB Powered w/ Remote Switching

Product ID: SV221NANOU



The SV221NANOU 2-Port USB VGA KVM Switch lets you control two computer systems using a single USB keyboard, mouse and VGA monitor.

The compact USB VGA KVM has a minimal footprint design that helps to organize your desk setup without sacrificing control or convenience. The switch features a push-button on a 1.5 meter (5ft) built-in cable that can be placed in an easily accessible location, and keyboard hot-keys for switching, making it easy to manage both of your connected computers. Saving further space and clutter, the cable KVM draws power from USB, eliminating the need for a bulky external power adapter.

Offering support for extremely high resolutions (up to 2048x1536), this KVM has the ability to drive large VGA displays with crystal clarity, for applications that require outstanding graphical output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Ideal for graphic and multimedia designers, engineers, and industries using CAD/CAM applications, where high resolution VGA display units are required
- Perfect for sharing computers and attached peripherals in the home or home office
- Great for PC test/burn-in computer control, saving the desk space required for two monitors, keyboards and mice
- Dual system control for single user workstations increasing user productivity in the office

Features

- Access two PCs with a single set of peripherals (Keyboard, Mouse, and Monitor)
- Space-saving design, minimal footprint
- Compatible with USB 1.1 specifications
- Select PCs by using push-button or Hot-key commands
- Supports SVGA, VGA, XGA, WXGA, UXGA, WUXGA, QXGA and multi-sync monitors
- Supports high resolutions of up to 2048x1536
- Supports DDC, DDC2, and DDC2B
- USB Powered - No external power adapter required
- Remote switch on 1.5m (5ft.) cable

Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

IP Control	No
Hot-Key Selection	Yes
Maximum Analog Resolutions	2048 x 1536(QXGA)
Wide Screen Supported	Yes



Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

Connector(s)

Console Interface(s)	USB Type-A (4 pin) USB 2.0 VGA (15 pin, High Density D-Sub)
Host Connectors	USB Type-A (4 pin) USB 2.0 VGA (15 pin, High Density D-Sub)

Software

OS Compatibility	Windows 2000/XP/Vista/7 Mac OS X 10.3/10.4/10.5/10.6 and Linux
------------------	---

Indicators

LED Indicators	Power indicator
----------------	-----------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 80C (14F to 176F)
Humidity	0~90% RH

Physical Characteristics

Color	Black
Material	Plastic
Product Width	2.3 in [59 mm]
Product Height	0.5 in [12 mm]
Product Depth	1.3 in [33 mm]
Weight of Product	7.4 oz [210 g]

Packaging Information

Package Length	9.3 in [23.5 cm]
Package Width	5.4 in [13.7 cm]



Package Height	1.3 in [32 mm]
Shipping (Package) Weight	10.0 oz [282.0 g]

What's in the Box

Included in Package	2 port USB KVM switch
	User Manual

****Product appearance and specifications are subject to change without notice.***

