

2 Port Professional PS/2 KVM Switch

Productcode: SV231



This 2 Port PS/2 KVM Switch is a reliable computer management tool that allows you to control multiple computers from one source, minimizing downtime by making connected computers and input devices available as soon as they are attached.

This sturdy PS/2 KVM Switch features an all-metal, 1U chassis that adds to the unit's reliability and dependability.

The PS/2 KVM switch is designed to work with Dell, Compaq, IBM and HP servers, all PC notebook computers, and Compaq Alpha systems, and supports resolutions of up to 1920x1440 - ensuring a smooth and broadly compatible operating experience.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

Certificaties, rapporten en compatibiliteit



Toepassingen

- Manufacturing line computer control
- PC test/burn-in computer control
- Dual system control for a single workstation

Eigenschappen

- A dependable 3-year warranty provides peace of mind.
- Hot-pluggable to allow computers to be added or removed without worrying about having to reboot the other connected systems.
- Designed for guaranteed compatibility with Dell, Compaq, IBM and HP servers and systems.
- Compatible with all notebook computers.
- Compatible with Compaq Alpha systems.
- "Keep-alive" feature draws power from PC keyboard ports if power is lost. Switch will continue to operate during a power outage retaining complete control of all connected systems.
- Rugged, all-metal 1U chassis for use in harsh environments and space-saving cabinets.
- Fast switch-buttons for each port provide quick access to any connected system.
- High 1920x1440 resolution capability supports the most demanding applications.
- Uses standard off-the-shelf cables or StarTech.com tangle-free KVM cables to connect PCs to the switch
- All cables connect to the back of the switch reducing space requirements
- Completely operating system independent. No software or drivers required.

Hardware

Garantiebeleid	3 Years
Audio	Nee
KVM-poorten	2
Ondersteunde platforms	PS/2
PC-videotype	VGA

Multi-monitor	1
Rack-monteerbaar	Nee
Inclusief kabels	Nee
Op elkaar aansluitbaar	Ja

Prestaties

Schermmenu & sneltoetsen	Nee
DVI-ondersteuning	Nee
IP-controle	Nee
Hot-Key Selection	Ja
Maximale analoge resoluties	1920 x 1440
Maximum aantal gebruikers	1
Max. op elkaar aansluitbare computers	4
Poortselectie-ondersteuning	Knopdruk en sneltoetsen
MTBF	111000 uur

Connector(en)

Console-aansluiting(en)	2 - PS/2 (6-polig, Mini-DIN)
	1 - VGA (15-polig, D-Sub met hoge dichtheid)
Hostaansluitingen	4 - PS/2 (6-polig, Mini-DIN)
	2 - VGA (15-polig, D-Sub met hoge dichtheid)

Software

Besturingssystemen	OS independent; No software or drivers required
--------------------	---

Gebruiksomgeving

Bedrijfstemperatuur	0°C to 40°C (32°F to 104°F)
---------------------	-----------------------------

Opslagtemperatuur	-10°C to 60°C (14°F to 140°F)
Vochtigheid	0~80% RH

Fysieke eigenschappen

Type behuizing	Staal
Lengte product	2.8 in [7.0 cm]
Breedte product	4.9 in [12.4 cm]
Hoogte product	1.6 in [4.0 cm]
Gewicht product	15.1 oz [427.0 g]

Verpakkingsinformatie

Verpakkingsaantal	1
Lengte Verpakking	8.5 in [21.6 cm]
Package Width	6.0 in [15.2 cm]
Package Height	2.1 in [5.4 cm]
Verzendgewicht (verpakt)	1.3 lb [0.6 kg]

Wat wordt er meegeleverd

Meegeleverd	1 - 2 Port StarView 2 KVM Switch
	2 - PS/2 Mouse Connectors
	4 - Rubber feet
	1 - Instruction Manual
	1 - Hot-key Quick Reference

Garantiebepalingen

Warranty	3 Jaar
----------	--------

* Uitvoering en specificaties van het product zijn zonder aankondiging vatbaar voor wijzigingen.