

## 2 Port Professional PS/2 KVM Switch

Produkt ID: SV231



This 2 Port PS/2 KVM Switch is a reliable computer management tool that allows you to control multiple computers from one source, minimizing downtime by making connected computers and input devices available as soon as they are attached.

This sturdy PS/2 KVM Switch features an all-metal, 1U chassis that adds to the unit's reliability and dependability.

The PS/2 KVM switch is designed to work with Dell, Compaq, IBM and HP servers, all PC notebook computers, and Compaq Alpha systems, and supports resolutions of up to 1920x1440 - ensuring a smooth and broadly compatible operating experience.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

## Certifikat, rapporter och kompatibilitet

### Användning

- Manufacturing line computer control
- PC test/burn-in computer control
- Dual system control for a single workstation

### Funktioner

- A dependable 3-year warranty provides peace of mind.
- Hot-pluggable to allow computers to be added or removed without worrying about having to reboot the other connected systems.
- Designed for guaranteed compatibility with Dell, Compaq, IBM and HP servers and systems.
- Compatible with all notebook computers.
- Compatible with Compaq Alpha systems.
- "Keep-alive" feature draws power from PC keyboard ports if power is lost. Switch will continue to operate during a power outage retaining complete control of all connected systems.
- Rugged, all-metal 1U chassis for use in harsh environments and space-saving cabinets.
- Fast switch-buttons for each port provide quick access to any connected system.
- High 1920x1440 resolution capability supports the most demanding applications.
- Uses standard off-the-shelf cables or StarTech.com tangle-free KVM cables to connect PCs to the switch
- All cables connect to the back of the switch reducing space requirements
- Completely operating system independent. No software or drivers required.

---

#### Hårdvara

Garantipolicy	3 Years
Audio	Nej
KVM-portar	2
PC-gränssnitt	PS/2
PC-videotyp	VGA
Flera skärmar	1
Hyllmonterbar	Nej
Medföljande kablar	Nej
Kedjekoppling	Ja

---

#### Prestanda



Skärmvisning (OSD) & stöd för snabbtangenter	Nej
DVI-stöd	Nej
IP-kontroll	Nej
Hot-Key Selection	Ja
Maximal analog upplösning	1920 x 1440
Maximalt antal användare	1
Maximalt antal överlappade datorer	4
Stöd för portval	Tryckknapp och genvägskommandon
Medeltid mellan fel (MTBF)	111000 hours

---

#### Kontakt(er)

Konsolgränssnitt	PS/2 (6-stifts, Mini-DIN)
	VGA (15-stifts, High Density D-Sub)
Värdkontakter	PS/2 (6-stifts, Mini-DIN)
	VGA (15-stifts, High Density D-Sub)

---

#### Mjukvara

OS-kompatibilitet	OS independent; No software or drivers required
-------------------	---

---

#### Miljö

Drifttemperatur	0°C to 40°C (32°F to 104°F)
Förvaringstemperatur	-10°C to 60°C (14°F to 140°F)
Luftfuktighet	0~80% RH

---

#### Utseende

Kabinetttyp	Stål
Produktlängd	2.8 in [70 mm]



Produktbredd	4.9 in [12.4 cm]
Produkt höjd	1.6 in [40 mm]
Produktvikt	15.1 oz [427 g]

---

#### Förpackning

Package Length	5.9 in [15.1 cm]
Package Width	8.5 in [21.7 cm]
Package Height	2.0 in [52 mm]
Fraktvikt (förpackning)	21.7 oz [614 g]

---

#### Vad det är i lådan

Ingår i paketet	2 Port StarView 2 KVM Switch
	PS/2 Mouse Connectors
	Rubber feet
	Instruction Manual
	Hot-key Quick Reference

---

\* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

