

2 Port Professional PS/2 KVM Switch

Product ID: SV231



This 2 Port PS/2 KVM Switch is a reliable computer management tool that allows you to control multiple computers from one source, minimizing downtime by making connected computers and input devices available as soon as they are attached.

This sturdy PS/2 KVM Switch features an all-metal, 1U chassis that adds to the unit's reliability and dependability.

The PS/2 KVM switch is designed to work with Dell, Compaq, IBM and HP servers, all PC notebook computers, and Compaq Alpha systems, and supports resolutions of up to 1920x1440 - ensuring a smooth and broadly compatible operating experience.

This product is TAA compliant and is backed by a Startech.com 3 year warranty with lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Manufacturing line computer control
- PC test/burn-in computer control
- Dual system control for a single workstation

Features

- A dependable 3-year warranty provides peace of mind.
- Hot-pluggable to allow computers to be added or removed without worrying about having to reboot the other

connected systems.

- Designed for guaranteed compatibility with Dell, Compaq, IBM and HP servers and systems.
- Compatible with all notebook computers.
- Compatible with Compaq Alpha systems.
- "Keep-alive" feature draws power from PC keyboard ports if power is lost. Switch will continue to operate during a power outage retaining complete control of all connected systems.
- Rugged, all-metal 1U chassis for use in harsh environments and space-saving cabinets.
- Fast switch-buttons for each port provide quick access to any connected system.
- High 1920x1440 resolution capability supports the most demanding applications.
- Uses standard off-the-shelf cables or StarTech.com tangle-free KVM cables to connect PCs to the switch
- All cables connect to the back of the switch reducing space requirements
- Completely operating system independent. No software or drivers required.

Hardware

Warranty	3 Years
Audio	No
KVM Ports	2
PC Interface	PS/2
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	No
Daisy-Chain	Yes

Performance

On-Screen Display	No
DVI Support	No
IP Control	No



Hot-Key Selection	Yes
Maximum Analog Resolutions	1920 x 1440
Maximum Number of Users	1
Maximum Cascaded Computers	4
Port Selection Support	Push Button and Hotkeys
MTBF	111000 hours

Connector(s)

Console Interface(s)	VGA (15 pin, High Density D-Sub)
	PS/2 (6 pin, Mini-DIN)
Host Connectors	VGA (15 pin, High Density D-Sub)
	PS/2 (6 pin, Mini-DIN)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-10C to 60C (14F to 140F)
Humidity	0~80% RH

Physical Characteristics

Material	Steel
Product Length	2.8 in [70 mm]
Product Width	4.9 in [12.4 cm]
Product Height	1.6 in [40 mm]
Weight of Product	15.1 oz [427 g]

Packaging Information

Package Length	5.9 in [15.1 cm]
----------------	------------------



Package Width	8.5 in [21.7 cm]
Package Height	2.0 in [52 mm]
Shipping (Package) Weight	21.7 oz [614 g]

What's in the Box

Included in Package	2 Port StarView 2 KVM Switch
	Instruction Manual
	Rubber feet
	PS/2 Mouse Connectors
	Hot-key Quick Reference

****Product appearance and specifications are subject to change without notice.***

