

## 2 Port SuperSpeed USB 3.0 Dual Link DVI KVM Switch with Audio and Cables

**Product ID:** SV231DLU3A



The SV231DLU3A 2 Port SuperSpeed USB 3.0 Dual-Link DVI KVM Switch with Audio and Cables lets you control 2 DVI, USB 3.0 equipped PCs with a single monitor, keyboard, mouse and audio peripheral set.

This USB 3.0 KVM Switch offers an integrated 2 port hub that supports USB 3.0 data rates of up to 5 Gbps, and is backward compatible with USB 2.0 and 1.1/1.0 devices, ensuring flawless performance for your USB peripherals.

Offering support for high resolutions (up to 2560x1600), this 2 port Dual-link DVI KVM switch has the ability to drive large Dual-link DVI displays with ease, ideal for graphical applications that require high-res video output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility

### Applications

- Ideal for financial/banking industries, graphic designers, multi-media applications and industries using CAD/CAM applications
- Integrated USB 3.0 hub and Mic/Audio allows the user to have full multimedia control of two computers and share USB peripherals in a home or office
- Control two DVI USB computers with a single set of console peripherals (Keyboard, Mouse, and Monitor)

### Features

- Access two Dual-Link DVI USB PCs with one set of Keyboard, Mouse, Monitor and Audio peripherals

- Integrated USB 3.0 (5 Gbps) hub
- Hot-key and front-panel push buttons for easy computer selection
- Video, audio and USB cables included
- USB keyboard and mouse console connections
- Supports resolutions up to 2560x1600
- No software or drivers required
- Stereo audio and microphone support

---

#### Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB 3.0
PC Video Type	DVI
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

---

#### Performance

On-Screen Display	No
IP Control	No
Hot-Key Selection	Yes
Maximum Cable Length	32.8 ft [10 m]
Maximum Digital Resolutions	2560 x 1600
Audio Specifications	2-Channel Stereo supported
Port Selection Support	Push Button and Hotkeys



MTBF 141,836 Hours

---

**Connector(s)**

Console Interface(s)	DVI-I (29 pin) USB Type-A (4 pin) USB 2.0 3.5 mm Mini-Jack (3 Position)
Host Connectors	DVI-I (29 pin) USB Type-B (9 pin) USB 3.0 3.5 mm Mini-Jack (3 Position)
Other Interface(s)	USB Type-A (9 pin) USB 3.0 (5 Gbps)

---

**Software**

OS Compatibility	OS independent; No software or drivers required
------------------	---

---

**Indicators**

LED Indicators	PC Selection Indicator Hub selection indicator
----------------	---

---

**Power**

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	0.5 A
Output Voltage	9V DC
Output Current	2 A
Center Tip Polarity	Positive
Plug Type	M

---

**Environmental**

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 40C (4F to 104F)
Humidity	0~90% RH Non-Condensing

---



**Physical Characteristics**

Color	Black
Material	Steel
Cable Length	4.0 ft [1.2 m]
Product Length	6.5 in [16.5 cm]
Product Width	3.5 in [89 mm]
Product Height	1.8 in [46 mm]
Weight of Product	21.2 oz [600 g]

**Packaging Information**

Package Length	8.1 in [20.7 cm]
Package Width	5.6 in [14.1 cm]
Package Height	7.1 in [18 cm]
Shipping (Package) Weight	3.9 lb [1.8 kg]

**What's in the Box**

Included in Package	2 Port USB 3.0 KVM Switch
	DVI M/M Cables
	USB 3.0 A-B Cables
	3.5mm Audio/Mic Cables
	Universal Power Adapter (NA/UK/EU)
	Instruction Manual

***\*Product appearance and specifications are subject to change without notice.***

