

2-port DisplayPort KVM Switch - USB 2.0 - 4K 30Hz

Product ID: SV231DPU2



This versatile USB KVM switch lets you share a DisplayPort workstation with two computer systems, providing control of a DP monitor, keyboard & mouse, plus an additional USB peripheral device.

To ensure compatibility with your setup, this KVM switch was rigorously tested with the most popular platforms including Windows, Linux and Mac computers, and is powered through your USB peripherals, meaning you won't require an external power source.

With support for resolutions up to 4K at 30hz you'll be amazed at how this DisplayPort KVM flawlessly manages your graphics-intensive content. At four times the resolution of high-definition 1080p, this lossless performance makes the switch ideal solution for high-resource applications such as graphic design, CAD / CAM design, or health care imaging (MRI, radiology diagnostics, etc.).

Plus, the KVM switch also supports 1080p displays, which makes it a great accessory for home, office or other workspace applications.

Featuring DisplayPort 1.1 with 7.1 digital audio, plus a 3-port USB hub for your keyboard, mouse and an additional USB peripheral device, this KVM switch is perfect for accessing two separate systems using the same workstation - ideal for server control, simplifying access to multiple computer systems.

This 2-port KVM delivers effortless operation with hardware and software switching, providing a simple yet comprehensive solution for switching between each connected computer. The switching software that's included gives you on-demand switching using an intuitive video interface. Hotkey control is also available when working with Windows computers, plus the switch features an easy-to-access toggle switch located on the front.

The SV231DPU2 is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Control two computer systems from a single workstation
- View the high-resolution video output on medical and healthcare equipment such as MRI and X-Ray machines
- Edit high resolution video through the KVM switch
- View the video output of satellite topography equipment with console control

Features

- Astonishing picture quality with support for video resolutions up to 4K
- Maximum productivity with multi-system access
- Hassle-free operation with hotkey and push-button switching (hot keys supported in Windows only)
- 7.1 digital audio support
- Full plug-and-play support with USB keyboards, mice, and connected peripherals
- Supports resolutions up to 3840 x 2160 @ 30Hz
- No driver or software required
- Supports DDC2B pass through
- Works with Mini-DisplayPort, HDMI, and DVI adapters

Hardware

Warranty	2 Years
Audio	No
KVM Ports	2
PC Interface	USB
PC Video Type	DisplayPort
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Industry Standards	HDCP 2.2



Daisy-Chain No

Performance

On-Screen Display	No
Video Revision	DisplayPort 1.1
DVI Support	Yes - Dual Link
IP Control	No
Hot-Key Selection	Yes
Maximum Digital Resolutions	4K - 3840 x 2160 @ 30Hz (supporting video source and display required)
Wide Screen Supported	Yes
Audio Specifications	7.1 digital audio (dependent on supporting display and video sources)
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys
General Specifications	To achieve the maximum resolution of 4K at 30Hz, a video source and display that support that resolution are required. Hotkey switch commands are only supported when using Windows computers.

Connector(s)

Console Interface(s)	DisplayPort (20 pin) USB Type-A (4 pin) USB 2.0
Host Connectors	DisplayPort (20 pin) USB B (4 pin)

Special Notes / Requirements

Note	For audio support the display must support DisplayPort audio, and the source and display must have compatible DisplayPort revisions
------	---

Indicators

LED Indicators	Port 1 active LED
----------------	-------------------



Port 2 active LED

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0~80% RH

Physical Characteristics

Color	Black
Cable Length	3.9 ft [1.2 m]
Product Length	7.0 in [17.7 cm]
Product Width	3.2 in [82.0 mm]
Product Height	1.0 in [25.0 mm]
Weight of Product	12.2 oz [346.0 g]

Packaging Information

Package Length	9.6 in [24.3 cm]
Package Width	7.5 in [19.0 cm]
Package Height	2.8 in [72.0 mm]
Shipping (Package) Weight	31.3 oz [888.0 g]

What's in the Box

Included in Package	2-Port DisplayPort KVM Switch
	4 ft (1.2 m) DisplayPort KVM Cables
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

