

2 Port SuperSpeed USB 3.0 DisplayPort KVM Switch with Audio and Cables

Product ID: SV231DPU3A



The SV231DPU3A 2 Port SuperSpeed USB 3.0 DisplayPort KVM Switch with Audio and Cables lets you control 2 DisplayPort, USB 3.0 equipped PCs with a single monitor, keyboard, mouse and audio peripheral set.

This USB 3.0 KVM Switch offers an integrated 2 port hub that supports USB 3.0 data rates of up to 5 Gbps, and is backward compatible with USB 2.0 and 1.1/1.0 devices, ensuring flawless performance for your USB peripherals.

Offering support for high resolutions (up to 2560x1600), this 2 port DisplayPort KVM switch has the ability to drive large DisplayPort displays with ease, ideal for graphical applications that require high-res video output.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Control two DisplayPort USB computers with a single set of console peripherals (Keyboard, Mouse, and Monitor)
- Ideal for financial/banking industries, graphic designers, multi-media applications and industries using CAD/CAM applications
- Integrated USB 3.0 hub and Mic/Audio allows the user to have full multimedia control of two computers and share USB peripherals in a home or office

Features

- Access two DisplayPort USB PCs with one set of Keyboard, Mouse, Monitor and Audio peripherals

- Integrated USB 3.0 (5 Gbps) hub
- Hot-key and front-panel push buttons for easy computer selection
- Video, audio and USB cables included
- USB keyboard and mouse console connections
- Supports resolutions up to 2560x1600
- No software or drivers required
- Stereo audio and microphone support

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB 3.0
PC Video Type	DisplayPort
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

IP Control	No
Hot-Key Selection	Yes
Maximum Cable Length	32.8 ft [10 m]
Maximum Digital Resolutions	2560 x 1600
Audio Specifications	2-Channel Stereo supported
Port Selection Support	Push Button and Hotkeys
MTBF	173,702 Hours



Connector(s)

Console Interface(s)	3.5 mm Mini-Jack (3 Position) DisplayPort (20 pin) USB Type-A (4 pin) USB 2.0
Host Connectors	3.5 mm Mini-Jack (3 Position) DisplayPort (20 pin) USB Type-B (9 pin) USB 3.0
Other Interface(s)	USB Type-A (9 pin) USB 3.0 (5 Gbps)

Software

OS Compatibility	OS independent; No software or drivers required
------------------	---

Indicators

LED Indicators	Hub selection indicator PC Selection Indicator
----------------	---

Power

Power Source	AC Adapter Included
Input Voltage	110V-240V AC
Input Current	0.5 A
Output Voltage	9V DC
Output Current	2 A
Center Tip Polarity	Positive
Plug Type	M

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 40C (4F to 104F)
Humidity	0~90% RH Non-Condensing

Physical Characteristics

Color	Black
-------	-------



Material	Steel
Cable Length	4.0 ft [1.2 m]
Product Length	6.5 in [16.5 cm]
Product Width	3.5 in [89 mm]
Product Height	1.8 in [46 mm]
Weight of Product	33.2 oz [940 g]

Packaging Information

Package Length	8.1 in [20.7 cm]
Package Width	5.6 in [14.1 cm]
Package Height	7.1 in [18 cm]
Shipping (Package) Weight	2.3 lb [1.0 kg]

What's in the Box

Included in Package	2 Port USB 3.0 KVM Switch
	DisplayPort M/M Cables
	USB 3.0 A-B Cables
	3.5mm Audio/Mic Cables
	Universal Power Adapter (NA/UK/EU)
	Instruction Manual

****Product appearance and specifications are subject to change without notice.***

