

## 2 Port Professional USB DisplayPort KVM Switch with Hotkey Control

**Product ID:** SV231DPU



This 2-Port USB DisplayPort KVM Switch combines the next generation of digital display interface standards with seamless KVM control of connected PC or Mac computers.

Delivering ideal multi-computer control for demanding high-resolution multimedia applications, or computer environments requiring true high definition capability, the robust KVM switch supports DisplayPort connections with a native resolution of 2560 x 1600 (@60 Hz, 30 bpp), as well as 7.1 HD digital audio (when connected to supporting displays and sources).

Suitable for applications that utilize high quality static imaging, such as medical/health care applications (MRI, X-ray diagnostics etc.), the KVM switch supports a maximum resolution of 3840 x 2400 at a reduced refresh rate.

Adding cost-effective performance to cutting-edge multimedia capability, this versatile KVM switch features three Plug-and-Play USB console ports, including two dedicated peripheral (mouse and keyboard) ports and one USB 2.0 hub port - enabling users to share a USB mouse and keyboard, and one USB 2.0 peripheral between the two connected Mac or PC computers.

A simple, yet comprehensive control solution, the 2-port KVM switch features both front-panel push-button and convenient hotkey switching and offers a small form factor design with connection ports situated on the rear panel, allowing you to eliminate workspace disruptions.

The SV231DPU DisplayPort KVM switch is backed by our 3-year warranty and free lifetime technical support, guaranteeing dependable, long-lasting performance.

## Certifications, Reports and Compatibility





## Applications

- Ideal for multimedia design, post-production and video editing using Mac or PC computers
- Provide centralized control for multiple high-res Digital Signage server control
- Useful in high resolution medical imaging and Health care displays, such as MRI and Xray display
- Good for manufacturing line computer control, simplifying access to multiple systems
- Great for PC test/burn-in computer control saving the desk space required for two monitors, keyboards and mice
- Dual system control for single user workstations increasing user productivity in the office
- Consolidate your Satellite Topography systems into a single console

## Features

- StarTech.com is the first to introduce a DisplayPort KVM into the Market
- OS independent - No driver or software installation required
- Native resolution: 2560 x 1600 @ 60Hz, beyond 1080p
- Hot-key and push-button switching
- Supports a maximum resolution of 3840 x 2400 at lower refresh rates
- Supports native DisplayPort computer connections - no adapter required
- Compatible with Mini-DisplayPort adapters
- 7.1 Channel High Definition Audio support
- USB 2.0 peripheral sharing
- Full plug-and-play support with USB keyboards, mice, and connected peripherals
- Supports hot-plug or disconnect and link status-failure detection
- VESA and CEA compliant
- User-defined scan time intervals
- Supports DDC2B for monitor detection
- Direct Drive support

---

## Hardware

Warranty	3 Years
Audio	Yes
KVM Ports	2
PC Interface	USB
PC Video Type	DisplayPort
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

---

## Performance

On-Screen Display	No
DVI Support	Yes - Dual Link
IP Control	No
Hot-Key Selection	Yes
Maximum Digital Resolutions	2560 x 1600 @ 60Hz
Wide Screen Supported	Yes
Maximum Number of Users	1
Port Selection Support	Push Button and Hotkeys

---

## Connector(s)

Console Interface(s)	1 - DisplayPort (20 pin) 3 - USB 2.0 Type-A (4 pin, 480Mbps)
Host Connectors	2 - DisplayPort (20 pin) 2 - USB B (4 pin)

<b>Software</b>	OS Compatibility	OS independent; No software or drivers required
<b>Indicators</b>	LED Indicators	2 - Green - Online indicator (One LED per port)
		2 - Red - Select indicator (One LED per port)
<b>Power</b>	Power Source	AC Adapter Included
	Input Voltage	110V-240V AC
	Input Current	0.4A
	Output Voltage	5 DC
	Output Current	2A
	Center Tip Polarity	Positive
	Plug Type	N
<b>Physical Characteristics</b>	Color	Black
	Material	Steel
	Product Width	5.0 in [12.6 cm]
	Product Height	1.6 in [4 cm]
	Product Depth	2.6 in [65 mm]
	Weight of Product	14.7 oz [417.3 g]
<b>Packaging Information</b>	Package Length	9.4 in [23.9 cm]
	Package Width	4.0 in [10.2 cm]
	Package Height	8.5 in [21.5 cm]
	Shipping (Package) Weight	3.0 lb [1.3 kg]

## What's in the Box

Included in Package	1 - 2 port DisplayPort KVM
	1 - Rubber Feet
	1 - Universal Power Adapter (US/UK/EU)
	1 - Manual

---

***\*Product appearance and specifications are subject to change without notice.***